

10HPEND1-HG

✓ ACTIVE

Corcom | Corcom HP

TE Internal #: 1-1609157-0

Multi-Function Inlet Filters, Power Entry Module, None Input, DPST, Complete Shield, Locking Socket & Shrouded Output, 1 MOPP, Vertical, Corcom HP

[View on TE.com >](#)



EMI & EMC Solutions > EMI Filters > Multi-Function Inlet Filters



Filter Type: **Power Entry Module**
Input Voltage Selection: **None**
Filter Switch Type: **DPST**
Filter Shield Type: **Complete Shield**
Filter Safety Features: **Locking Socket & Shrouded Output**

Features

Product Type Features

Ground Choke Option	No
Level Of Filtering	Inductor & Capacitor
Filter Type	Power Entry Module
Filter Switch Type	DPST
Output Termination Type	.187" FASTON
Filtering Requirements	Filtered
Filter Connector Type	IEC 60320-1 C-14

Configuration Features

Fuse Options	Dual
--------------	------

Electrical Characteristics

Input Voltage Selection	None
Leakage Current (Max) (120VAC, 60Hz)	3 μ A
Leakage Current (Max) (250VAC, 50Hz)	5 μ A
Current Rating	10 A



Operating Voltage	250 VAC
-------------------	---------

Body Features

Filter Shield Type	Complete Shield
Product Orientation	Vertical

Mechanical Attachment

Panel Mount Feature Type	Mounting Ears (Vertical)
--------------------------	--------------------------

Dimensions

Panel Thickness (Recommended)	1 – 2 mm[.039 – .079 in]
-------------------------------	--------------------------

Usage Conditions

Operating Temperature Range	-40 – 40 °C
-----------------------------	-------------

Operation/Application

Filter Safety Features	Locking Socket & Shrouded Output
Filter Mode of Operation	1 MOPP

Industry Standards

Agency/Standard	UL
-----------------	----

Other

EMI Filters Comment	Limit fault current to 12 A at 40C. Use low-leakage power cord.
---------------------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as



EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 6-1609158-8
[10HPEND1-NG=F8534](#)



TE Part # 4-1609158-0
[10HPENS1=F8506](#)

Also in the Series | Corcom HP



[Multi-Function Inlet Filters\(96\)](#)

Customers Also Bought



TE Part #1375820-5
[CST-100 II HOUSING 5 POS](#)



TE Part #1-499252-0
[024 STRAIN RELIEF A-L RCPT](#)



TE Part #440133-3
[2.5MM,HSG,3POS](#)



TE Part #1-1393238-2
[RTB14005](#)

10HPEND1-HG

Multi-Function Inlet Filters, Power Entry Module, None Input, DPST, Complete Shield, Locking Socket & Shrouded Output, 1 MOPP, Vertical, Corcom HP






TE Part #1658621-5
24 NOVO MIL/CTR 15DP,LEAD FREE



TE Part #6-2176328-1
CRGP 1206 1M0 1%



TE Part #6609103-8
PE0S0DH6B=C1253



TE Part #177537-3
2.5 M.I.S POST HDR ASSY 3P



TE Part #8-1609158-5
12HPEGD1-HG=F8556

TE Part #NB-PTCO-045
Pt100, 2.0x10.0, Class A, PTFB101AG00

Documents

Product Drawings

10HPEND1-HG=F8571

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1609157-0_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1609157-0_1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1609157-0_1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

HP SERIES EMI FILTERS

English

Corcom HP series EMI PEM Filters

English

Agency Approvals

UL

English

10HPEND1-HG

Multi-Function Inlet Filters, Power Entry Module, None Input, DPST, Complete Shield,
Locking Socket & Shrouded Output, 1 MOPP, Vertical, Corcom HP

