




Connectors > Connector Accessories > Connector Backshells > Connector Backshell Accessories: Cable Clamp, Tool-less Assembly



Connector Backshell Product Type: **Cable Clamp & Body**

Number of Positions: **1**

Sealable: **No**

Compatible With Connector Shape: **Rectangular**

Operating Temperature Range: **-55 – 175 °C [-67 – 347 °F]**

[All Connector Backshell Accessories: Cable Clamp, Tool-less Assembly \(2\)](#)

Features

Product Type Features

Connector Backshell Product Type	Cable Clamp & Body
Sealable	No

Configuration Features

Number of Positions	1
---------------------	---

Housing Features

Compatible With Connector Shape	Rectangular
---------------------------------	-------------

Usage Conditions

Operating Temperature Range	-55 – 175 °C[-67 – 347 °F]
-----------------------------	----------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # ZPF000000000100828
DMC-MD 20 A

Customers Also Bought



TE Part #ZPF000000000100828
Rectangular Connector Plugs, Tool-less Assembly



TE Part #ZPF000000000145736
DMC-MD 26 C-K-T



TE Part #ZPF00000000017893
FAST-E 07 F-X-B 00 A



TE Part #ZPF000000000003599
724-0003-22



TE Part #ZPF000000000015291
DMC-M 20-22 AN

TE Part #ZPF000000000015299
DMC-M 20-22 BN

TE Part #ZPF000000000017897
FAST-E 08 F-X-B 00 A

TE Part #ZPF0000000000103303
787-8009-00

TE Part #605705-31
CONT PIN

Documents

Product Drawings

787-8055-17M

English

787-8055-17M

French

CAD Files

Customer View Model

ENG_CVM_CVM_ZPF000000000204892_F.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_ZPF000000000204892_F.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_ZPF000000000204892_F.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

DEUTSCH DMC-MD Shielded Cable Clamp

English