



Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Wire**

Number of Positions: **9**

Centerline (Pitch): **5.03 mm [.198 in]**

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	9
Number of Signal Positions	9
Number of Rows	3

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Contact Layout	Matrix
Contact Retention Within Housing	Without



Contact Type	Socket
--------------	--------

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Panel Mount Feature	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	5.03 mm[.198 in]
Housing Color	Natural
Housing Material	Nylon 6/6

Dimensions

Connector Height	16.89 mm
Product Width	16.13 mm
Product Length	25.4 mm
Row-to-Row Spacing	5.03 mm[.198 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

CSA Rating	Certified, LR 7189
UL Rating	Recognized
Agency/Standard	CSA, UL
Approved Standards	UL E28476
UL Flammability Rating	UL 94V-2
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 770096-1
.09P .093 COMM P&S PLUG

TE Part # 770144-1
.093 CP&S SOK PTPBR L/P 20-14

TE Part # 770147-1
.093 CP&S PIN PTPBR LP 24-18

TE Part # 350416-1
.093 COMM P&S PIN 14-20 PTPBR

TE Part # 770529-1
.093 COMM P&S SOK 14-20 PTPBR

TE Part # 770530-1
.093 COMM P&S PIN 14-20 PTPBR

TE Part # 350415-1
.093 COMM P&S SOK 14-20 PTPBR

TE Part # 350418-1
.093 COMM P&S PIN 18-24 PTPBR




 TE Part # 350417-1 .093 COMM P&S SOK 18-24 PTPBR	 TE Part # 350415-5 .093 COMM P&S SOK 20-14 AUBR	 TE Part # 770092-1 09P .093 COMM P&S RECPT HSG	 TE Part # 770095-1 09P .093 COMM P&S PLUG
 TE Part # 770145-1 .093 COMM P&S PIN PTPBR LP	 TE Part # 770146-1 .093 CP&S SOK PTPBR LP 24-18	 TE Part # 350416-5 .093 COMM P&S PIN AU/NI/BR	 TE Part # 770093-1 09P .093 COMM P&S RECPT
 TE Part # 770144-5 .093 CP&S SOC AUBR L/P 20-14	 TE Part # 350415-6 .093 COMM P&S SOK 14-20 PTPHBZ	 TE Part # 350417-5 .093 COMM P&S SOK AU/NI/BR	 TE Part # 770145-5 .093 CP&S PIN AUBR LP 20-14

Also in the Series | Commercial Pin and Socket Connectors

 Connector Contacts(2)	 Crimp Wire Pins, Tabs & Ferrules(1)	 Insertion & Extraction Tools(2)	 Power Contacts(39)
 Rectangular Connector Housings(10)	 Rectangular Power Connectors(84)	 Standard Rectangular Connectors(1)	

Customers Also Bought



TE Part #156667-1
PIDG FASTON FLAG ASSY 22-18



TE Part #1-770849-7
17P SL156 HSG W/LCK RAMP W/TBS




TE Part #1-1623732-9
BCHE 7 W 1R5 10%



TE Part #770105-1
15P .093 COMM P&S RECPT



TE Part #1-87159-2
12 MODI CRMP S-I HSG SR .156CL



TE Part #770144-6
.093 CP&S SOC PTPPHBZ LP 20-14

TE Part #87717-000
PS822-002 PROXIMITY SENSOR

TE Part #87725-000
PS701-01 PROXIMITY SENSOR

TE Part #87765-000
PS825-011 PROXIMITY SENSOR

Documents

Product Drawings

09P .093 COMM P&S RECPT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_770094-1_L.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_770094-1_L.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_770094-1_L.3d_stp.zip

English

3D PDF

English



Customer View Model

[ENG_CVM_770094-1_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_770094-1_E.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_770094-1_E.2d_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[CSA Certificate](#)

English