




Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > FFC Contacts >
2.54mm FFC Connectors Pin Contacts



Centerline (Pitch): 2.54 mm [.1 in]

Compatible With Wire & Cable Type: FFC

Contact Type: Pin

Contact Mating Area Plating Material: Tin

Packaging Method: Reel

[All 2.54mm FFC Connectors Pin Contacts \(34\)](#)

Features

Product Type Features

Connector & Contact Terminates To	Wire & Cable
-----------------------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	FFC
-----------------------------------	-----

Contact Features

	100 µin
PCB Contact Termination Area Plating Material	Gold Flash
Contact Base Material	Phosphor Bronze
Contact Type	Pin
Contact Mating Area Plating Material	Tin
Contact Current Rating (Max)	2 A

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Housing Features



Centerline (Pitch)	2.54 mm[.1 in]
--------------------	----------------

Dimensions

Accepts Conductor Width	1.27 mm[.05 in]
-------------------------	-----------------

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Method	Reel
------------------	------

Other

Connector Contacts Comment	For use in housings.
----------------------------	----------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>










EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # CAT-F439-S01339254 2.54mm FFC Connectors Socket Contacts	 TE Part # 88117-9 FFC PIN CONT 15AU RL	 TE Part # CAT-F439-R2435254 2.54mm FFC Connectors Receptacle Housing	 TE Part # 485893-5 007 HOUSING FFC PIN 100CL SR
 TE Part # 485893-8 010 HOUSING FFC PIN 100CL SR	 TE Part # 485893-9 011 HOUSING FFC PIN 100CL SR	 TE Part # 1-485893-4 016 HOUSING FFC PIN 100CL SR	 TE Part # 3-88189-2 006 HOUSING FFC PIN DR 100CL
 TE Part # 1-88189-0 026 HOUSING FFC PIN DR 100CL	 TE Part # 3-88189-0 010 HOUSING FFC PIN DR 100CL	 TE Part # 485897-2 004 HOUSING FFC PIN 100CL SR	 TE Part # 1-485893-6 018 HOUSING FFC PIN 100CL SR
 TE Part # 1-485893-8 020 HOUSING FFC PIN 100CL SR	 TE Part # 3-88190-0 010 HOUSING FFC PIN DR 100CL	 TE Part # 485893-6 008 HOUSING FFC PIN 100CL SR	 TE Part # 485893-3 005 HOUSING FFC PIN 100CL SR
 TE Part # 485893-4 006 HOUSING FFC PIN 100CL SR	 TE Part # 485893-2 004 HOUSING FFC PIN 100CL SR	 TE Part # 1-485893-1 013 HOUSING FFC PIN 100CL SR	 TE Part # 1-485893-3 015 HOUSING FFC PIN 100CL SR

Customers Also Bought





TE Part #487378-4
2.54mm FFC Connectors Receptacle Housing



TE Part #2-487406-4
FFC,RCPT CONTACT,STD PRESSURE



TE Part #1-88997-2
FFC S.TAB 100SN RL



TE Part #YDTS26F11-35PNV001
PLUG ASSY



TE Part #382312-009
44A0121-24-0/9



TE Part #316035-006
55A1121-24-2/6-9



TE Part #1-485893-0
012 HOUSING FFC PIN 100CL SR



TE Part #L9000111-01
Antenna Dome 2.4GHz 1.32 216 UFL

Documents

Product Drawings

FFC,PIN CONTACT,.025" SQ

English

CAD Files

Customer View Model

ENG_CVM_CVM_88117-7_AZ.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_88117-7_AZ.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_88117-7_AZ.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Application Specification

English

Product Environmental Compliance

Product Compliance

English



Product Compliance

English

Instruction Sheets

Instruction Sheet (U.S.)

English