



Connectors > PCB Connectors > Backplane Connectors > Backplane Guide Hardware



Connector Guide Hardware Type: **Guide Socket Module**

Features

Product Type Features

Connector Guide Hardware Type	Guide Socket Module
-------------------------------	---------------------

Configuration Features

PCB Mount Orientation	Right Angle
-----------------------	-------------

Body Features

Guide Component Plating Material Finish Process	Chromate Conversion Coating
---	-----------------------------

Housing Features

Guide Housing Material	Zinc Alloy
------------------------	------------

Dimensions

Product Length	22.5 mm[.886 in]
----------------	------------------

Operation/Application

Compatible With Backplane Product Type	VITA 41 Guide Pin
--	-------------------

Industry Standards

VITA Standard	VITA 41
---------------	---------

Packaging Features

Packaging Quantity	250
Packaging Method	Carton



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1410963-9
VITA 41 KEYED GUIDE PIN



Customers Also Bought





TE Part #1-2199119-5
M.2 0.5PITCH 3.2H KEY M 15U" AU



TE Part #2309407-1
DDR4 SODIMM 260P 4.0H STD




TE Part #650470-5
096 EURO TYPE R PIN ST ASSY



TE Part #2-5767004-2
MICTOR RECEPT ASSY, 38 POS.




TE Part #2-2013290-1
EMBOSS TAPE DDR3 204P 5.2H RVS



TE Part #1-829315-0
2X10P MOD2 STIFTLI



TE Part #2201778-1
MICRO SD PUSH PUSH LOW PROFILE TYPE



TE Part #1-1571986-1
A101J1AV2Q004=SGL POLE,ROCKER TYPE



TE Part #41481
250 FASTON TAB TPBR



TE Part #1483350-3
MICRO-MATCH LEAD 04P 250MM

Documents

Product Drawings

VITA 41 KEYED GUIDE MODULE

English

CAD Files

Customer View Model

ENG_CVM_CVM_1410465-9_A.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1410465-9_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1410465-9_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



[2_PIECE_POWER_CONNECTORS_qrg_4-1773458-1](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[MD_1410465-9_03082013346_dmtec](#)

English

[MD_1410465-9_03082013346_dmtec](#)

English