




Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Grommet Seal**

Primary Product Material: **Silicone**

Primary Product Color: **Red**

Compatible Insulation Diameter Range: **1.4 – 2.1 mm [ .055 – .083 in ]**

Shore A Hardness: **50**

Features

Product Type Features

Connector Seal & Plug Type	Grommet Seal
----------------------------	--------------

Body Features

Primary Product Material	Silicone
Primary Product Color	Red

Dimensions

Compatible Insulation Diameter Range	1.4 – 2.1 mm[.055 – .083 in]
--------------------------------------	------------------------------

Packaging Features

Packaging Quantity	10000
Packaging Method	Bag

Other

Shore A Hardness	50
Contains Lubricant	No

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5-1437710-6  
NP1TA-00R2XX=CONN. 2W MALE  
WAT




TE Part # 2-1437712-2  
MP1NA-1008XX=CONN. 8W FEMA  
BLK

Also in the Series | Timer Connector System



Automotive Connector Caps & Covers (12)



Automotive Connector Locks & Position Assurance (17)



Automotive Housings (234)



Automotive Terminals (145)



Connector Seals & Cavity Plugs (32)




Crimp Terminal Housings (13)




Insertion & Extraction Tools (18)



Other Automotive Connector Accessories (1)



PCB Headers & Receptacles (82)



Quick Disconnects (4)

Customers Also Bought



TE Part #927365-1  
Timer Connector Housing




TE Part #965785-1  
ABDECKKAPPE 180GRD




TE Part #163300-8  
MATENLOK SOCKET



TE Part #805M1-0200-01  
805M1-0200-01 TO-5 Accelerometer



TE Part #1-967402-1  
2,5MM ST-GEH KPL 4P




TE Part #929967-1  
STIFTKONTAKT 2,5MMD



TE Part #444046-1  
HSG ASSY 4POS MULTI



TE Part #62820-1  
PIN 093 CRIMP TAB 22-16 AWG PTPBR



Documents

Product Drawings

106100=GROMMET RED

English

106100=GROMMET RED

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1-1437713-2\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-1437713-2\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-1437713-2\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.