




MTA 156

TE Internal #: 4-640601-2

Rectangular Power Connectors, Connector Assembly, Receptacle, Wire-to-Board, 12 Position, 3.96 mm [.156 in] Centerline, Wire & Cable, MTA 156

[View on TE.com >](#)

Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Connector Assembly**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **12**

Centerline (Pitch): **3.96 mm [.156 in]**

Features

Product Type Features

|                                    |                    |
|------------------------------------|--------------------|
| Compatible With Discrete Wire Type | Stranded           |
| Rectangular Power Connector Type   | Connector Assembly |
| Connector & Housing Type           | Receptacle         |
| Connector System                   | Wire-to-Board      |
| Sealable                           | No                 |
| Connector & Contact Terminates To  | Wire & Cable       |

Configuration Features

|                           |    |
|---------------------------|----|
| Number of Positions       | 12 |
| Number of Power Positions | 12 |
| Number of Rows            | 1  |

Electrical Characteristics

|                   |         |
|-------------------|---------|
| Operating Voltage | 600 VAC |
|-------------------|---------|

Body Features

|                  |     |
|------------------|-----|
| Cable Exit Angle | 90° |
|------------------|-----|



|                                                 |                               |
|-------------------------------------------------|-------------------------------|
| Connector Profile                               | Standard                      |
| Contact Features                                |                               |
| Contact Layout                                  | Inline                        |
| Contact Underplating Material Thickness         | 30 µm[.762 µin]               |
| Wire Contact Termination Area Plating Thickness | 2.03 – 5.08 µm[80 – 200 µin]  |
| Contact Mating Area Plating Material            | Tin                           |
| Contact Mating Area Plating Material Finish     | Matte                         |
| Contact Underplating Material                   | Nickel                        |
| Contact Base Material                           | Copper Alloy                  |
| Contact Current Rating (Max)                    | 7 A                           |
| Contact Retention Within Housing                | With                          |
| Contact Type                                    | Receptacle                    |
| Wire Contact Termination Area Plating Material  | Tin                           |
| Contact Mating Area Plating Material Thickness  | 2.03 µm[80 µin]               |
| Termination Features                            |                               |
| Termination Method to Wire & Cable              | Insulation Displacement (IDC) |
| Mechanical Attachment                           |                               |
| Strain Relief                                   | With                          |
| Mating Retention                                | With                          |
| Mating Alignment                                | Without                       |
| Contact Retention Type Within Housing           | Locking Lance                 |
| PCB Mount Alignment                             | Without                       |
| Panel Mount Feature                             | Without                       |
| PCB Mount Retention                             | Without                       |
| Mating Retention Type                           | Locking Ramp                  |
| Connector Mounting Type                         | Cable Mount (Free-Hanging)    |
| Housing Features                                |                               |
| Wire & Cable IDC Installation Type              | Feed Through                  |
| Centerline (Pitch)                              | 3.96 mm[.156 in]              |
| Housing Color                                   | Red                           |
| Housing Material                                | Nylon                         |
| Dimensions                                      |                               |
|                                                 |                               |



|                                      |                      |
|--------------------------------------|----------------------|
| Connector Height                     | 9.78 mm[.385 in]     |
| Product Length                       | 47.55 mm[1.872 in]   |
| Compatible Insulation Diameter Range | 2.41 mm[.095 in]     |
| Wire Size                            | .325 mm <sup>2</sup> |

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -55 – 105 °C[-67 – 221 °F] |
|-----------------------------|----------------------------|

Operation/Application

|                     |       |
|---------------------|-------|
| Circuit Application | Power |
|---------------------|-------|

Industry Standards

|                        |                               |
|------------------------|-------------------------------|
| CSA Rating             | Certified, LR 7189            |
| UL Rating              | Recognized                    |
| Agency/Standard        | CSA, UL                       |
| Approved Standards     | UL E28476                     |
| UL Flammability Rating | UL 94V-2                      |
| Glow Wire Rating       | Standard Part - Not Glow Wire |

Packaging Features

|                    |           |
|--------------------|-----------|
| Packaging Quantity | 250       |
| Packaging Method   | Bag & Box |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2023 (235)<br>Candidate List Declared Against: JUNE 2023 (235)<br>Does not contain REACH SVHC |
| Halogen Content                               | BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.                                                                          |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                    |







Product Compliance Disclaimer





This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

|                                                                                                                                                      |                                                                                                                                                    |                                                                                                                                                               |                                                                                                                                                                    |
|------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  <p>TE Part # 58074-1<br/>MTA 50/100/156 MANUAL TOOL<br/>FRAME</p> |  <p>TE Part # 59804-1<br/>MAINTENANCE TOOL</p>                   |  <p>TE Part # 58443-1<br/>MTA 156 CRIMP HEAD PRODUCTION<br/>FEED THRU</p> |  <p>TE Part # 1-640384-2<br/>12P MTA156 HDR ASSY STR RND SN<br/>FEED THRU</p> |
|  <p>TE Part # 4-641435-2<br/>12P MTA156 CONN ASSY ORNG</p>        |  <p>TE Part # 1-640385-2<br/>12P MTA156 HDR ASSY SQ R/A</p>     |  <p>TE Part # 1-640389-2<br/>12P MTA156 HDR ASSY SQ R/A F/L</p>          |  <p>TE Part # 1-640551-2<br/>12P MTA156 COVER</p>                             |
|  <p>TE Part # 1-640388-2<br/>12P MTA156 HDR ASSY RN STR F/L</p>   |  <p>TE Part # 1-644752-2<br/>12P MTA156 HDR ASSY SQ STR F/L</p> |  <p>TE Part # 1-640445-2<br/>12P MTA156 HDR ASSY FL/STR SN</p>           |  <p>TE Part # 1-640383-2<br/>12P MTA156 HDR ASSY STR SQ SN</p>                |
|  <p>TE Part # 1-643067-2<br/>12P MTA156 MOLDED COVER</p>          |  <p>TE Part # 1-643071-2<br/>12P MTA156 FD-THRU COVER</p>       |  <p>TE Part # 3-647123-2<br/>12P MTA156 SHRD HDR ASSY SQ SN</p>          |  <p>TE Part # 1-644753-2<br/>12P MTA156 HDR ASSY RN STR F/L</p>               |





TE Part # 4-644617-2  
12P MTA156 HDR ASY PO RA FB LF

TE Part # 641876-3  
12P MTA156 HDR ASSY FL STR SN

TE Part # 1-640643-2  
12P MTA156 COVER F/T

TE Part # 1-644751-2  
12P MTA156 HDR ASSY R/A

Also in the Series | MTA 156

Insertion & Extraction Tools(1)

PCB Connector Covers(88)

PCB Connector Keying(2)

PCB Connector Mounting(1)

PCB Headers & Receptacles(314)

Power Contacts(2)

Rectangular Power Connectors(698)

Standard Rectangular Connectors(337)

Wire-to-Board Connector Contacts(2)

Customers Also Bought

TE Part #207463-1  
CRIMP SNAP RCPT ASSY,SZ 3


TE Part #4-643813-2  
12P MTA100 CONN ASSY POL RIB

TE Part #1-643075-2  
12P MTA100 MOLDED COVER


TE Part #1-6609028-4  
10VK3=F7144 S0



TE Part #5796055-1  
68 CHAMP R/A ASSY,LC



TE Part #4-640426-2  
12P MTA156 CONN ASSY 18AWG  
ORA



TE Part #1-640520-0  
06P MR II PLUG HSG



TE Part #3-640428-6  
06P MTA156 CONN ASSY 22AWG RED



TE Part #3-643819-6  
06P MTA156 CONN ASSY 22AWG RED



TE Part #3-641437-4  
04P MTA156 PSTD CONN ASSY RED

Documents

Product Drawings

12P MTA156 CONN ASSY 22AWG LF

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_4-640601-2\_R.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_4-640601-2\_R.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_4-640601-2\_R.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

Japanese

Application Specification

English

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

English

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

Japanese



---

**Product Environmental Compliance**

**Product Compliance**

English

**Product Compliance**

English

---

**Agency Approvals**

**CSA Certificate**

English