


# Optocoupler, Photodarlington Output, High Gain, 300 V BV<sub>CEO</sub>



23095



## FEATURES

- High collector emitter voltage,  $V_{CEO} = 300\text{ V}$
- Low coupling capacitance
- High common mode transient immunity
- Isolation rated voltage  $5000\text{ V}_{RMS}$
- Standard plastic DIP-4 package
- Material categorization:  
for definitions of compliance please see  
[www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS**  
COMPLIANT  
HALOGEN  
**FREE**  
**GREEN**  
(5-2008)

## DESIGN SUPPORT TOOLS AVAILABLE



3D Models



Design Tools



Related Documents

## DESCRIPTION

The SFH619A has a GaAs infrared emitting diode emitter, which is optically coupled to a silicon photodarlington detector, and is incorporated in a plastic DIP-4 package.

It features a high current transfer ratio, low coupling capacitance, and high isolation voltage.

The coupling device is designed for signal transmission between two electrically separated circuits.

## APPLICATIONS

- Telecom
- Industrial controls
- Battery powered equipment
- Office machines
- Programmable controllers

## AGENCY APPROVALS

- [UL](#)
- [cUL](#)
- [CQC](#)

## ORDERING INFORMATION

|                                                                                                                                                                                                                                                                      |  |  |  |  |  |  |                              |  |  |  |  |  |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--|--|--|--|--|------------------------------|--|--|--|--|--|
| <div><div><div>S</div><div>F</div><div>H</div><div>6</div><div>1</div><div>9</div><div>A</div><div>-</div><div>X</div><div>0</div><div>0</div><div>#</div><div>T</div></div><div><div>PART NUMBER</div><div>PACKAGE OPTION</div><div>TAPE AND REEL</div></div></div> |  |  |  |  |  |  |                              |  |  |  |  |  |
| AGENCY CERTIFIED / PACKAGE                                                                                                                                                                                                                                           |  |  |  |  |  |  | CTR (%)                      |  |  |  |  |  |
| UL, BSI, FIMKO                                                                                                                                                                                                                                                       |  |  |  |  |  |  | ≥ 1000                       |  |  |  |  |  |
| DIP-4                                                                                                                                                                                                                                                                |  |  |  |  |  |  | SFH619A                      |  |  |  |  |  |
| SMD-4, option 7                                                                                                                                                                                                                                                      |  |  |  |  |  |  | SFH619A-X007T <sup>(1)</sup> |  |  |  |  |  |
| SMD-4, option 9                                                                                                                                                                                                                                                      |  |  |  |  |  |  | SFH619A-X009T <sup>(1)</sup> |  |  |  |  |  |

## Notes

- Additional options may be possible, please contact sales office
- <sup>(1)</sup> Also available in tubes; do not put T on the end

| <b>ABSOLUTE MAXIMUM RATINGS</b> ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified) |                   |            |             |                    |
|--------------------------------------------------------------------------------------------------------|-------------------|------------|-------------|--------------------|
| PARAMETER                                                                                              | TEST CONDITION    | SYMBOL     | VALUE       | UNIT               |
| <b>INPUT</b>                                                                                           |                   |            |             |                    |
| Reverse voltage                                                                                        |                   | $V_R$      | 6           | V                  |
| Forward current                                                                                        |                   | $I_F$      | 50          | mA                 |
| Power dissipation                                                                                      |                   | $P_{diss}$ | 70          | mW                 |
| <b>OUTPUT</b>                                                                                          |                   |            |             |                    |
| Collector emitter voltage                                                                              |                   | $V_{CEO}$  | 300         | V                  |
| Emitter collector voltage                                                                              |                   | $V_{ECO}$  | 0.3         | V                  |
| Collector current                                                                                      |                   | $I_C$      | 125         | mA                 |
| Power dissipation                                                                                      |                   | $P_{diss}$ | 150         | mW                 |
| <b>COUPLER</b>                                                                                         |                   |            |             |                    |
| Total power dissipation                                                                                |                   | $P_{tot}$  | 200         | mW                 |
| Storage temperature                                                                                    |                   | $T_{stg}$  | -55 to +125 | $^{\circ}\text{C}$ |
| Operating temperature                                                                                  |                   | $T_{amb}$  | -55 to +100 | $^{\circ}\text{C}$ |
| Soldering temperature                                                                                  | $t = 10\text{ s}$ | $T_{sld}$  | 260         | $^{\circ}\text{C}$ |

**Note**

- Stresses in excess of the absolute maximum ratings can cause permanent damage to the device. Functional operation of the device is not implied at these or any other conditions in excess of those given in the operational sections of this document. Exposure to absolute maximum ratings for extended periods of the time can adversely affect reliability




Fig. 1 - Power Dissipation vs. Ambient Temperature




Fig. 2 - Maximum Forward Current vs. Ambient Temperature

| <b>ELECTRICAL CHARACTERISTICS</b> ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified) |                                                                   |             |      |      |      |               |
|----------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------|-------------|------|------|------|---------------|
| PARAMETER                                                                                                | TEST CONDITION                                                    | SYMBOL      | MIN. | TYP. | MAX. | UNIT          |
| <b>INPUT</b>                                                                                             |                                                                   |             |      |      |      |               |
| Forward voltage                                                                                          | $I_F = 10\text{ mA}$                                              | $V_F$       | -    | 1.2  | 1.5  | V             |
| Reverse current                                                                                          | $V_R = 6\text{ V}$                                                | $I_R$       | -    | 0.02 | 10   | $\mu\text{A}$ |
| Capacitance                                                                                              | $V_R = 0\text{ V}$                                                | $C_I$       | -    | 30   | -    | pF            |
| <b>OUTPUT</b>                                                                                            |                                                                   |             |      |      |      |               |
| Collector emitter breakdown voltage                                                                      | $I_{CE} = 100\text{ }\mu\text{A}$                                 | $BV_{CEO}$  | 300  | -    | -    | V             |
| Emitter collector breakdown voltage                                                                      | $I_{EC} = 100\text{ }\mu\text{A}$                                 | $BV_{ECO}$  | 0.3  | -    | -    | V             |
| Collector emitter leakage current                                                                        | $V_{CE} = 200\text{ V}$ , $T_{amb} = 25\text{ }^{\circ}\text{C}$  | $I_{CEO}$   | -    | 10   | 200  | nA            |
|                                                                                                          | $V_{CE} = 200\text{ V}$ , $T_{amb} = 100\text{ }^{\circ}\text{C}$ | $I_{CEO}$   | -    | -    | 20   | $\mu\text{A}$ |
| <b>COUPLER</b>                                                                                           |                                                                   |             |      |      |      |               |
| Collector emitter saturation voltage                                                                     | $I_F = 1\text{ mA}$ , $I_C = 10\text{ mA}$                        | $V_{CEsat}$ | -    | -    | 1    | V             |
| Coupling capacitance                                                                                     | $V_{I-O} = 0\text{ V}$ , $f = 1\text{ MHz}$                       | $C_{IO}$    | -    | 0.6  | -    | pF            |

**Note**

- Minimum and maximum values are testing requirements. Typical values are characteristics of the device and are the result of engineering evaluation. Typical values are for information only and are not part of the testing requirements

| <b>CURRENT TRANSFER RATIO</b> |                                             |        |      |      |      |      |
|-------------------------------|---------------------------------------------|--------|------|------|------|------|
| PARAMETER                     | TEST CONDITION                              | SYMBOL | MIN. | TYP. | MAX. | UNIT |
| $I_C/I_F$                     | $I_F = 1\text{ mA}$ , $V_{CE} = 1\text{ V}$ | CTR    | 1000 | -    | -    | %    |

| <b>SWITCHING CHARACTERISTICS</b> |                                                                          |           |      |      |      |               |
|----------------------------------|--------------------------------------------------------------------------|-----------|------|------|------|---------------|
| PARAMETER                        | TEST CONDITION                                                           | SYMBOL    | MIN. | TYP. | MAX. | UNIT          |
| Turn-on time                     | $V_{CC} = 10\text{ V}$ , $I_F = 5\text{ mA}$ , $R_L = 100\text{ }\Omega$ | $t_{on}$  | -    | 6.5  | -    | $\mu\text{s}$ |
| Turn-off time                    | $V_{CC} = 10\text{ V}$ , $I_F = 5\text{ mA}$ , $R_L = 100\text{ }\Omega$ | $t_{off}$ | -    | 72   | -    | $\mu\text{s}$ |




Fig. 3 - Test Circuit for Switching Characteristics




Fig. 4 - Parameter and Limit Definition

**SAFETY AND INSULATION RATINGS**

| PARAMETER                                    | TEST CONDITION                                      | SYMBOL     | VALUE          | UNIT       |
|----------------------------------------------|-----------------------------------------------------|------------|----------------|------------|
| Climatic classification                      | According to IEC 68 part 1                          |            | 55 / 115 / 21  |            |
| Pollution degree                             | According to DIN VDE 0109                           |            | 2              |            |
| Comparative tracking index                   | Insulation group IIIa                               | CTI        | 175            |            |
| Maximum rated withstanding isolation voltage | According to UL1577, t = 1 min                      | $V_{ISO}$  | 5000           | $V_{RMS}$  |
| Maximum transient isolation voltage          | According to DIN EN 60747-5-5                       | $V_{IOTM}$ | 8000           | $V_{peak}$ |
| Maximum repetitive peak isolation voltage    | According to DIN EN 60747-5-5                       | $V_{IORM}$ | 890            | $V_{peak}$ |
| Isolation resistance                         | $V_{IO} = 500\text{ V}$ , $T_{amb} = 25\text{ °C}$  | $R_{IO}$   | $\geq 10^{12}$ | $\Omega$   |
|                                              | $V_{IO} = 500\text{ V}$ , $T_{amb} = 100\text{ °C}$ | $R_{IO}$   | $\geq 10^{11}$ | $\Omega$   |
| Output safety power                          |                                                     | $P_{SO}$   | 700            | mW         |
| Input safety current                         |                                                     | $I_{SI}$   | 400            | mA         |
| Input safety temperature                     |                                                     | $T_S$      | 175            | °C         |
| Creepage distance                            |                                                     |            | $\geq 7$       | mm         |
| Clearance distance                           |                                                     |            | $\geq 7$       | mm         |
| Insulation thickness                         |                                                     | DTI        | $\geq 0.4$     | mm         |

**Note**

- As per IEC 60747-5-5, § 7.4.3.8.2, this optocoupler is suitable for “safe electrical insulation” only within the safety ratings. Compliance with the safety ratings shall be ensured by means of protective circuits.


**TYPICAL CHARACTERISTICS** ( $T_{amb} = 25\text{ °C}$ , unless otherwise specified)


Fig. 5 - Forward Current vs. Forward Voltage




Fig. 6 - Collector Current vs. Collector Emitter Voltage (non-saturated)




Fig. 7 - Collector Current vs. Collector Emitter Voltage (saturated)




Fig. 10 - Voltage Gain vs. Frequency




Fig. 8 - Leakage Current vs. Ambient Temperature




Fig. 11 - Switching Time vs. Load Resistance









Fig. 9 - Normalized CTR vs. Forward Current

**PACKAGE DIMENSIONS** in millimeters

**4 Pin Package**

**Option 7**


20802-51




**Option 9**

**PACKAGE MARKING**


Fig. 12 - Example of SFH619A

**Note**

- Tape and reel suffix (T) is not part of the package marking

**PACKAGING INFORMATION**

| DEVICES PER TUBE |            |           |           |
|------------------|------------|-----------|-----------|
| TYPE             | UNITS/TUBE | TUBES/BOX | UNITS/BOX |
| DIP-4            | 100        | 40        | 4000      |
| SMD-4, option 7  | 100        | 40        | 4000      |
| SMD-4, option 9  | 100        | 40        | 4000      |


**DIP-4 Tube**


Fig. 13 - Tube


**SMD-4 Tape**


Fig. 14 - Tape and Reel Packaging (1000 pieces on reel)


**Reel**


Fig. 15 - Tape and Reel Shipping Medium

**SOLDER PROFILES**
**IR Reflow Soldering (JEDEC® J-STD-020C compliant)**

One time soldering reflow is recommended within the condition of temperature and time profile shown below. Do not solder more than three times.

| PROFILE ITEM                                   | CONDITIONS       |
|------------------------------------------------|------------------|
| Preheat                                        |                  |
| - Temperature minimum ( $T_{S \text{ min.}}$ ) | 150 °C           |
| - Temperature maximum ( $T_{S \text{ max.}}$ ) | 200 °C           |
| - Time (min. to max.) ( $t_S$ )                | 90 s ± 30 s      |
| Soldering zone                                 |                  |
| - Temperature ( $T_L$ )                        | 217 °C           |
| - Time ( $t_L$ )                               | 60 s             |
| Peak temperature ( $T_p$ )                     | 260 °C           |
| Ramp-up rate                                   | 3 °C/s max.      |
| Ramp-down rate                                 | 3 °C/s to 6 °C/s |




Fig. 16





**Wave Soldering (JEDEC JESD22-A111 compliant)**

One time soldering is recommended within the condition of temperature.

Temperature:  $260\text{ }^{\circ}\text{C} + 0\text{ }^{\circ}\text{C} / - 5\text{ }^{\circ}\text{C}$

Time: 10 s

Preheat temperature:  $25\text{ }^{\circ}\text{C}$  to  $140\text{ }^{\circ}\text{C}$

Preheat time: 30 s to 80 s

**Hand Soldering by Soldering Iron**

Allow single lead soldering in every single process. One time soldering is recommended.

Temperature:  $380\text{ }^{\circ}\text{C} + 0\text{ }^{\circ}\text{C} / - 5\text{ }^{\circ}\text{C}$

Time: 3 s max.




Fig. 17



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.