




Terminals & Splices > PCB Terminals



PCB Terminal Type: **Receptacle**
PCB Hole Diameter: **5.2 mm [.161 in]**
Mating Pin Diameter: **1.47 mm [.058 in]**
Compatible Insulation Diameter (Max): **2.29 mm [.09 in]**
Compatible Insulation Diameter Range: **1.52 – 2.29 mm [.06 – .09 in]**

Features

Product Type Features

Terminal Features	Stud Hole
Wire Insulation Support Retention Type	Open Barrel

Contact Features

PCB Terminal Type	Receptacle
Mating Pin Diameter	1.47 mm[.058 in]
Terminal Plating Material	Pre-Tin
Terminal Size	Miniature
Terminal Orientation	Straight

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
Product Terminates To	Wire & Cable

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------



Dimensions

Terminal Material Thickness	.25 mm[.01 in]
PCB Hole Diameter	5.2 mm[.161 in]
Compatible Insulation Diameter (Max)	2.29 mm[.09 in]
Compatible Insulation Diameter Range	1.52 – 2.29 mm[.06 – .09 in]
Wire Size	.2 – .6 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




Compatible Parts

 TE Part # 60789-3 .058 DIA RECEPTACLE LP 20-24 GPPHBR	 TE Part # 60789-1 .058 DIA RECEPTACLE LP 20-24	 TE Part # 60940-1 .058 PIN REC 24-20 010PTPPHBZ	 TE Part # 350393-1 058 PCB REC IP 010PTPHBZ
 TE Part # 60983-2 .058 PIN REC PTPPHBZ	 TE Part # 61276-2 .058 DIA RECPT LP 24-20	 TE Part # 61018-1 .058 PCB PIN PTPPHBZ	 TE Part # 170137-1 ,058 DIA P.C.B REC LP
 TE Part # 60789-8 .058 DIA RECEPTACLE LP 20-24 GPBECU	 TE Part # 60789-2 .058 DIA RECEPTACLE LP 20-24	 TE Part # 60940-2 058 PIN REC 24-20 SN/BECU	

Customers Also Bought

 TE Part #1-179553-2 DYNAMIC D-3200S TAB HSG 2P K/X	 TE Part #160834-2 PIDG PIGGY-B FASTON	 TE Part #1-175217-2 DYNAMIC D-3 REC CONT. M AU 0.38 L/P	 TE Part #640917-2 RECEPT,PIDG FASTON 22-18 187 L/P
 TE Part #2176082-9 EP 3W (S) 220R 5%	 TE Part #3-643813-2 02P MTA100 CONN ASSY POL RIB	 TE Part #61907-1 187 FASTON TAB TPBR	 TE Part #3-1393117-0 KUP-11A55-24=KU



Documents

Product Drawings

.058 DIA PIN RECPT L/P

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_60986-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_60986-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_60986-1_B.3d_stp.zip

English

Customer View Model

ENG_CVM_60986-1_R1.3d_igs.zip

English

Customer View Model

ENG_CVM_60986-1_R1.3d_stp.zip

English

Customer View Model

ENG_CVM_60986-1_R1.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

PRINTED CIRCUIT BOARD TERMINALS AND DISCONNECTS

English

Product Specifications

Application Specification

English



Product Environmental Compliance

[TE Material Declaration](#)

English

Instruction Sheets

[Application and Maintenance for Hand Crimping Tool](#)

English

[Instruction Sheet \(U.S.\)](#)

English