



Sensors > Temperature Sensors > RTD Sensors > RTD Sensor Elements > Pt1000 RTD Thin Film Element



RTD Element Type: **Platinum Thin Film Temperature Element**

Tolerance Class: **Class A / F0.15**

Element Package: **Ceramic**

Element Material: **Platinum**

Lead Wire Style: **Ag**

[All Pt1000 RTD Thin Film Element \(26\)](#)

Features

Product Type Features

Wire/Cladding Type	Ag
Model Number	PTFD102A1A0
RTD Element Type	Platinum Thin Film Temperature Element
Element Material	Platinum
Lead Wire Style	Ag

Configuration Features

Connector Type	Open Ends
----------------	-----------

Dimensions

Height (Body)	1.1 mm[.043 in]
Wire Length	10 mm[.393 in]
Wire Diameter	.3 mm[.011 in]
Length (Body)	5 mm[.197 in]
Width (Body)	2 mm[.078 in]

Usage Conditions

Resistance (at T_ref)	1000 (0 °C) Ω
T_ref for Accuracy	0 °C



Ambient Temperature Range	-30 – 300 °C[-22 – 572 °F]
T1 and T2 for TCR	0 and +100 °C
TCR at (T1 and T2)	3850 ppm/°C
Accuracy (at T_ref)	± .15 °C
T_ref for Resistance	0 °C
Maximum Temperature	300 °C[572 °F]

Packaging Features

Element Package	Ceramic
-----------------	---------

Other

Tolerance Class	Class A / F0.15
Wire Count	2

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # NB-PTCO-168  
Pt1000, 2.0x5.0, Class A, PTFD102A1G0

Also in the Series | MEAS PTF



RTD Sensor Elements(53)

Customers Also Bought



TE Part #5120531-1  
1FHR,64,30A/S,N,C,S14,15



TE Part #6-1625984-5  
Power Resistors: Aluminum Housed, HSA



TE Part #3-1437603-8  
DPS9131AK=1-2-4-8 BCD CODE



TE Part #4-1393250-0  
W28-XQ1A-7=W28



TE Part #11032562-00  
44004RC,THERM,ROHS



TE Part #225291-E  
M12 M 8 A L90F T \* 301 \* 188 \*\* Y \* 000



TE Part #254538-E  
SMCQ 32 M AB VV 8-03 CL \* H007 137 E005

TE Part #225242-E  
M12 M 5 A L90F T \* 301 \* 188 \*\* Y \* 000

TE Part #BDA108F05000150000  
923 BULKHEAD CONNECTOR



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_NB-PTCO-170\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_NB-PTCO-170\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_NB-PTCO-170\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Datasheet PTF-Family PTFC,PTFD,PTFF,PTFM

English