



Sensors > Position Sensors > Potentiometer Sensors > Cable Actuated Position Sensors > SM, MINI STRING POT SERIES



Cable Actuated Position Sensor Product Type: **SM, Mini String Pot Series**

Full Stroke Ranges: **63.5 – 635 mm [7.5 in]**

Output Signal: **Voltage Divider (Potentiometric)**

Cable Actuated Position Sensor Accuracy: **.25 % of FS**

Repeatability: **.02 % of FS**

[All SM, MINI STRING POT SERIES \(4\)](#)

Features

Product Type Features

Cable Actuated Position Sensor Product Type	SM, Mini String Pot Series
---	----------------------------

Signal Characteristics

Output Signal	Voltage Divider (Potentiometric)
---------------	----------------------------------

Body Features

Cable Actuated Position Sensor Housing Material	Polycarbonate + Stainless Mounting Bracket
---	--

Usage Conditions

Operating Temperature Range	-18 – 71 °C[0 – 160 °F]
-----------------------------	-------------------------

Operation/Application

Resolution	Continuous Analog mm
------------	----------------------

Industry Standards

IP Rating	IP50
Hazardous Area Approval	No

Other

Full Stroke Ranges	63.5 – 635 mm[7.5 in]
Cable Actuated Position Sensor Accuracy	.25 % of FS



Repeatability	.02 % of FS
Encoder Drive	No
Measuring Cable	Nylon-Coated Stainless Steel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-CAPS0065
SM, MINI STRING POT SERIES



TE Part # CAT-CAPS0066
SM, MINI STRING POT SERIES

Also in the Series | MEAS SM



Cable Actuated Position Sensors(8)

Customers Also Bought



TE Part #926300-1
6P UNIV.M-N-L.PLUG



TE Part #640586-1
08P UMNL PLUG HSG V2 NATL



TE Part #926869-3
UNIV-MNL SOCKET 1



TE Part #41581
RT .171 DIA TERMINAL 24-20 AWG
TPBR



TE Part #926883-1
UNIVERSAL M-N-L PIN



TE Part #336075-3
250 FASTON,REC.,20-16 AWG,PTBR



TE Part #964280-6
JPT A REC 2.8 Contact SRC Ag

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_SM1-7_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_SM1-7_1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_SM1-7_1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SM1

English

