



Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Connector Hardware



Connector Hardware Type: **Strain Relief Clamp**
Number of Positions: **50**
Operating Temperature Range: **-55 – 150 °C [-67 – 302 °F]**

Features

Configuration Features

Number of Positions	50
---------------------	----

Body Features

Thread Lead Type	Rolled
Strain Relief Type	Shield & Cable Clamp
Primary Product Material	Stainless Steel
Cable Exit Angle	180°, 90°

Mechanical Attachment

Strain Relief	With
Mounting Hardware	U Bolt, Wire Guide, Protection Sleeve and Nut
Thread Size	8-32
Connector Hardware Type	Strain Relief Clamp

Dimensions

Product Width	25.4 mm[1 in]
Product Length	83.74 mm[3.297 in]
Product Height	65.89 mm[2.594 in]



Usage Conditions

Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Quantity	1
Packaging Method	Bag

Other

Connector Accessory Comment	Hardware supplied unassembled.
-----------------------------	--------------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 201182-4
STRAIN RELIEF CLAMP

Also in the Series | AMP M Series



Board-to-Board Jumpers & Shunts(7)




Rack & Panel Connectors(1)



Rectangular Connector Hardware(51)



Rectangular Power Connectors(66)




Standard Edge Connectors(2)

Customers Also Bought



TE Part #41729
250 FASTON REC 18-16 AWG TPBR



TE Part #1-87309-4
MOD V RECP LP



TE Part #1-1393118-4
KUP-14D15-24=KU-



TE Part #2-1437567-9
MPA106F=SWITCH P/B MOM SPDT



TE Part #4-1437558-3
MTA406N=(MSTA) SW TOG 4PDT



TE Part #2-1393766-2
R10-E1X6-V430=R10



TE Part #1-1624323-0
UPW50 0.1% 5PPM 250R



TE Part #1617031-1
HFW1201K00 = HFW 1/2 SIZE RELA



Documents

Product Drawings

50 PL. STR. REL. CLAMP

English

CAD Files

Customer View Model

ENG_CVM_201847-1_P.3d_igs.zip

English

Customer View Model

ENG_CVM_201847-1_P.3d_stp.zip

English

Customer View Model

ENG_CVM_201847-1_P.2d_dxf.zip

English

3D PDF

English

Customer View Model

ENG_CVM_CVM_201847-1_R.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_201847-1_R.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_201847-1_R.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

M_SERIES_PIN_AND_SOCKET_CONNECTORS

English

Instruction Sheets

Instruction Sheet (U.S.)

English



STRAIN RELIEF CLAMPS FOR AMP SERIES "M", COAXICON AND MINIATURE

English

Agency Approvals

Agency Approval Document

English