


EMI & EMC Solutions > EMI Filters > Multi-Function Inlet Filters



Filter Type: Power Entry Module

Input Voltage Selection: None

Filter Switch Type: DPST

Filter Shield Type: Complete Shield

Filter Safety Features: Locking Socket & Shrouded Output & Switch Guard

Features

Product Type Features

Ground Choke Option	No
Level Of Filtering	Inductor & Capacitor
Filter Type	Power Entry Module
Filter Switch Type	DPST
Output Termination Type	.187" FASTON
Filtering Requirements	Filtered
Filter Connector Type	IEC 60320-1 C-18

Configuration Features

Fuse Options	Dual
--------------	------

Electrical Characteristics

Input Voltage Selection	None
Leakage Current (Max) (120VAC, 60Hz)	3 µA
Leakage Current (Max) (250VAC, 50Hz)	5 µA
Current Rating	10 A

Operating Voltage	250 VAC
-------------------	---------

Body Features

Filter Shield Type	Complete Shield
Product Orientation	Vertical

Mechanical Attachment

Panel Mount Feature Type	Mounting Ears (Vertical)
--------------------------	--------------------------

Dimensions

Panel Thickness (Recommended)	1 – 2 mm [.039 – .079 in]
-------------------------------	---------------------------

Usage Conditions

Operating Temperature Range	-40 – 40 °C
-----------------------------	-------------

Operation/Application

Filter Safety Features	Locking Socket & Shrouded Output & Switch Guard
Filter Mode of Operation	2 MOOP

Industry Standards

Agency/Standard	UL
-----------------	----

Other

EMI Filters Comment	Limit fault current to 12 A at 40C. Use low-leakage power cord.
---------------------	---

Product Compliance

For compliance documentation, visit the product page on TE.com

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 2-1609158-0
10HPEGD1=F8486



TE Part # 8-1609158-4
10HPEGD1-HG=F8555

Also in the Series | Corcom HP



Multi-Function Inlet Filters(96)

Customers Also Bought



TE Part #1473416-2
SUPERSEAL Connector Housings: 1.0 mm

Documents

Product Drawings

[10HPEGD1-NG=F8518](#)

English

CAD Files[3D PDF](#)

3D

Customer View Model[ENG_CVM_CVM_5-1609158-2_1.2d_dxf.zip](#)

English

Customer View Model[ENG_CVM_CVM_5-1609158-2_1.3d_igs.zip](#)

English

Customer View Model[ENG_CVM_CVM_5-1609158-2_1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.**Datasheets & Catalog Pages**[HP SERIES EMI FILTERS](#)

English

[Corcom HP series EMI PEM Filters](#)

English

Agency Approvals[UL](#)

English