

201414-1

✓ ACTIVE

AMP


TE Internal #: 201414-1

Rectangular Connector Hardware, Jackscrew Kit, Turnable, Female

Jackscrew, 26 / 28 / 16 Position, -55 – 150 °C [-67 – 302 °F]

[View on TE.com >](#)

Connectors &gt; Rectangular Connectors &gt; Rectangular Connector Accessories &gt; Rectangular Connector Hardware

Connector Hardware Type: **Jackscrew Kit**Jackscrew Type: **Turnable**Jackscrew Style: **Female**Number of Positions: **12, 15, 16, 20, 26, 28, 34, 41, 42, 50**Operating Temperature Range: **-55 – 150 °C [-67 – 302 °F]**

## Features

### Configuration Features

Number of Positions	12, 15, 16, 20, 26, 28, 34, 41, 42, 50
---------------------	----------------------------------------

### Body Features

Thread Lead Type	Single
------------------	--------

Primary Product Material	Stainless Steel, Zinc Alloy
--------------------------	-----------------------------

### Mechanical Attachment

Primary Product Plating Finish	Non-Hexavalent Chromate
--------------------------------	-------------------------

Strain Relief	Without
---------------	---------

Mounting Hardware	Jackscrew Tip Female and Spirol Pin
-------------------	-------------------------------------

Thread Size	6-32
-------------	------

Connector Hardware Type	Jackscrew Kit
-------------------------	---------------

Jackscrew Type	Turnable
----------------	----------

Jackscrew Style	Female
-----------------	--------

### Dimensions

Product Width	7.92 mm [.312 in]
---------------	-------------------

Product Length	58.55 mm[2.305 in]
----------------	--------------------

Product Height	7.92 mm[.312 in]
----------------	------------------

### Usage Conditions

Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]
-----------------------------	----------------------------

### Packaging Features

Packaging Quantity	100
--------------------	-----

Packaging Method	Bag
------------------	-----

### Other

Connector Accessory Comment	Two required., Use turnable jackscrews on mating housings when mating to grounding block.
-----------------------------	-------------------------------------------------------------------------------------------

### Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com/compliance)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUN 2020 (209) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # 201414-4  
SERIES "M" JACK SCREW--FEMALE A

## Customers Also Bought



TE Part #201089-4  
SERIES "M" JACKSCREW SOCKET ASSY



TE Part #2-320568-3  
PIDG Ring Tongue Terminals



TE Part #324082  
TERMINAL, T-N R 8 1/4



TE Part #324047  
TERM, TERMINYL, RT, 6 AWG, 1/4



TE Part #1-200833-1  
SERIES "M" GUIDE PIN ST. STL.



TE Part #200517-9  
34 POS. SHIELD ASSY.

## Documents

### Product Drawings

#### SERIES "M" JACK SCREW--FEMALE A

English

### CAD Files

#### Customer View Model

[ENG\\_CVM\\_CVM\\_201414-1\\_J.2d\\_dxf.zip](#)

English

### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_201414-1\\_J.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_201414-1\\_J.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

**Instruction Sheets**

[Instruction Sheet \(U.S.\)](#)

English

[AMP Jack Screw Selection Chart for Series "M", COAXICON and Miniature](#)

English

[Instruction Sheet \(U.S.\)](#)

English

[AMP TURNABLE JACK SCREW SPECIFICATIONS AND ASSEMBLY INSTRUCTIONS](#)

English