

DTM04-12PD

✓ ACTIVE

DEUTSCH | DEUTSCH DT, DEUTSCH DTM

TE Internal #: DTM04-12PD

Housing for Male Terminals, Wire-to-Wire, 12 Position, .165 in [4.19 mm] Centerline, Sealable, Brown, Wire & Cable, Power & Signal, Hybrid

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Housings > DEUTSCH DTM Housings



Connector System: **Wire-to-Wire**  
Number of Positions: **12**  
Connector & Housing Type: **Housing for Male Terminals**  
Centerline (Pitch): **4.19 mm [ .165 in ]**  
Sealable: **Yes**

[All DEUTSCH DTM Housings \(109\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector System	Wire-to-Wire
Connector & Housing Type	Housing for Male Terminals
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Primary Locking Feature	Integrated in Housing

Configuration Features

Blank Cavity Position	0
Number of Positions	12
Number of Rows	2

Electrical Characteristics

Operating Voltage	250 VAC
Nominal Voltage Architecture	12 V, 24 V, 48 V

Body Features

Cable Exit Angle	180°
------------------	------



Primary Product Color	Brown
Connector & Keying Code	D

Contact Features

Contact Size	Size 20
Contact Type	Pin
Mating Pin Diameter	1.02 mm[.04 in]
Contact Current Rating (Max)	7.5 A

Mechanical Attachment

Terminal Position Assurance	Yes
Strain Relief	Add By Accessory
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PA GF
Centerline (Pitch)	4.19 mm[.165 in]

Dimensions

Connector Height	40.01 mm[1.575 in]
Product Width	20.22 mm[.796 in]
Product Length	43.69 mm[1.72 in]
Row-to-Row Spacing	7.11 mm[.28 in]
Compatible Insulation Diameter Range	1.35 – 3.05 mm[.053 – .12 in]

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Degree of Protection	IP68, IP6K9K
Agency/Standard	SAE J2030
UL Flammability Rating	20mm Flame Test per Standard UL-94

Packaging Features



Packaging Quantity	350
--------------------	-----

Packaging Method	Box
------------------	-----

Other

Serviceable	Yes
-------------	-----

Connector Position Assurance Capable	No
--------------------------------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Octamethylcyclotetrasiloxane (D4) (.5% in Component Part) Dodecamethylcyclohexasiloxane (D6) (.5% in Component Part) Decamethylcyclopentasiloxane (D5) (.5% in Component Part) <b>Article Safe Usage Statements:</b> Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
--	---

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
-----------------	--

Solder Process Capability	Not reviewed for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-D48-SP729  
DEUTSCH Sealing Plugs



TE Part # 1028-034-1205  
BKSHL, 12P, BLK, REC, ST, NW 13/17




TE Part # CAT-D485-CH8172  
DEUTSCH DTM Housings



TE Part # CAT-D485-W416  
DEUTSCH DTM Wedgelocks



TE Part # CAT-D487-M8649  
DEUTSCH DT Mounting Clips



TE Part # CAT-D48-ST273  
DEUTSCH Solid Contacts



TE Part # DTM12P-BT  
BOOT, 12P, REC, ST, GRY



TE Part # DTM12P-BT-BK  
BOOT, 12P, REC, ST, BLK



TE Part # 1924487-2  
MOUNTING CLIP, AMPSEAL 16



TE Part # 1011-055-1205  
SEAL RET, 12P, BRN, DTM, D



TE Part # DTM12P-DC  
PROTECT CVR, 12P, REC, GRY, DTM



TE Part # DT-RT1  
EXT TOOL, FRONT RELEASE



TE Part # 1060-20-0622  
PIN, SF, SIZE 20, 14-16, NI/NI



TE Part # 1060-20-0144  
PIN, SF, SIZE 20, 16-22, AU/SN



TE Part # 1060-20-0222  
PIN, SF, SIZE 20, 16-22, NI/NI



TE Part # 1060-20-0122  
PIN, SF, SIZE 20, 16-22, NI/NI




TE Part # 1060-20-0244  
PIN, SF, SIZE 20, 16-22, AU/SN



TE Part # 1060-20-0177  
PIN, SF, SIZE 20, 16-22, SN/SN



TE Part # 1060-20-0277  
PIN, SF, SIZE 20, 16-22, SN/SN




TE Part # CAT-D48-SFT273  
DEUTSCH Stamped and Formed  
Contacts

Also in the Series | **DEUTSCH DT**





Automotive Connector Caps & Covers (47)



Automotive Connector Locks & Position Assurance(74)



Automotive Housings(620)



Connector Backshells(58)




Connector Seals & Cavity Plugs(6)



Insertion & Extraction Tools(3)



Other Automotive Connector Accessories(27)




PCB Headers & Receptacles(103)

Also in the Series | **DEUTSCH DTM**



Automotive Connector Caps & Covers (35)



Automotive Connector Locks & Position Assurance(17)




Automotive Housings(100)



Connector Backshells(6)



Insertion & Extraction Tools(2)



PCB Headers & Receptacles(36)

Customers Also Bought

DTM04-12PD

Housing for Male Terminals, Wire-to-Wire, 12 Position, .165 in [4.19 mm] Centerline, Sealable, Brown, Wire & Cable, Power & Signal, Hybrid





TE Part #DTM04-12PB  
DEUTSCH DTM Housings



TE Part #WM-12P  
WEDGE LOCK, 12P, REC, ORG, DTM



TE Part #1-1969688-3  
PTL 1X3 PCB HEADER VERT HITEMP  
KEY A LGR



TE Part #DTM12P-BT-BK  
BOOT, 12P, REC, ST, BLK



TE Part #DT06-12SC-C015  
PLG, 12P, GRN, E, C



TE Part #3-1563878-1  
15POS, MIXED, REC HSG, SEALED,  
ASSY



TE Part #DTF13-4P-G003  
HDR, 4P, GRY, RA, AU/NI/CU



TE Part #62787-2  
RING TONGUE 18-14 AWG TPBR

Documents

Product Drawings

REC, 12P, BRN, N, D

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_DTM04-12PD\_99\_c-dtm04-12pd-99.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_DTM04-12PD\_99\_c-dtm04-12pd-99.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_DTM04-12PD\_99\_c-dtm04-12pd-99.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ICT Terminals and Connectors Catalogue

English

CONNECTOR SELECTOR

English

Product Specifications

Application Specification

English



[Agency Approvals](#)

[UL Report](#)

English