

1-2308273-1 ✓ ACTIVE

Rail D-Sub Backshells

TE Internal #: 1-2308273-1

Rectangular Connector Hardware, Quick Lock Pins, -40 – 90 °C [-40 – 194 °F], Rail D-Sub Backshells

[View on TE.com >](#)



Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Connector Hardware >

Quick Lock Pins for D-Sub Backshells



Connector Hardware Type: **Quick Lock Pins**

Operating Temperature Range: **-40 – 90 °C [-40 – 194 °F]**

[All Quick Lock Pins for D-Sub Backshells \(2\)](#)

Features

Mechanical Attachment

Thread Size **M3**

Connector Hardware Type **Quick Lock Pins**

Usage Conditions

Operating Temperature Range **-40 – 90 °C [-40 – 194 °F]**

Packaging Features

Packaging Quantity **500**

Packaging Method **Box**

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU

Compliant with Exemptions

EU ELV Directive 2000/53/EC

Compliant with Exemptions

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2023 (235)

Candidate List Declared Against: JUNE 2023 (235)

SVHC > Threshold:

Pb (3.5% in Component Part)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2308330-1
FULL METAL HOODS SIZE 4 (1)



TE Part # 1-2308338-1
QL-FULL METAL HOODS SIZE 5 (1 CABLE CLP)



TE Part # 1-2308319-1
FULL METAL HOODS SIZE 1 (1)




TE Part # 1-2308321-1
FULL METAL HOODS SIZE 2, (1)



TE Part # 1-2308327-1
FULL METAL HOODS SIZE 3 (1)


Also in the Series | Rail D-Sub Backshells




Connector Backshells(69)




Connector Strain Relief(53)




Crimp D-Sub Connectors(10)



D-Sub Connector Contacts(5)



Insertion & Extraction Tools(2)



Rectangular Connector Hardware(19)

Customers Also Bought

TE Part #2-2308265-0
QL SET FOR VARIANT B 10TE Part #170364-1
MINI UNIVERSAL M-N-L PIN LPTE Part #170366-1
MINI UNIVERSAL M-N-L SOCKET LPTE Part #172161-1
9 CIR UNIV M-N-L CAPTE Part #172169-1
9 CIR UNIV M-N-L PLUGTE Part #735410
ELECTRO TAP ASSYTE Part #34070
PG BUTT SPLC 22-16COMM22-18MILTE Part #1-2308290-1
QL-SET FOR VARIAN C VW REAR
WALL MOUNTG

Documents

Product Drawings

[QL-SET VAR A W/STP MO FOR COMBLOCK M3THD](#)

English

Datasheets & Catalog Pages

[Rail D-Sub Backshells Flyer](#)

English