



Connectors > Rectangular Connectors > Connector Contacts



Contact Type: **Tab**
Contact Mating Area Plating Material: **Gold**
Wire Contact Termination Area Plating Material: **Nickel**
Operating Voltage: **250 VDC, 600 VDC**

Features

Product Type Features

Discrete Wire Type	Stranded
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Electrical Characteristics

Operating Voltage	250 VDC, 600 VDC
-------------------	------------------

Contact Features

Contact Underplating Material Thickness	1.27 µm[50 µin]
Contact Mating Area Plating Material Thickness	.38 µm[15 µin]
Contact Shape & Form	Rectangular
Contact Length	25.3 mm[.996 in]
Contact Underplating Material	Nickel
Barrel Type	Open
Contact Type	Tab



Contact Mating Area Plating Material	Gold
Wire Contact Termination Area Plating Material	Nickel
Contact Retention Within Housing	With
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	10 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Contact Retention Type Within Housing	Locking Lance
---------------------------------------	---------------

Dimensions

Compatible Insulation Diameter Range	1.2 – 2.6 mm[.047 – .102 in]
Wire Size	24 – 20 AWG

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Identification Marking

Wire Range Mark	M
-----------------	---

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2-2151080-1
[OCEAN_2.0_APPLICATOR-S-062F110F](#)

TE Part # 2151080-1
[OCEAN_2.0_APPLICATOR-S-062F110F](#)

TE Part # 2151080-2
[OCEAN_2.0_APPLICATOR-S-062F110F](#)

TE Part # 7-2151080-1
[OCEAN_2.0_APPLICATOR-S-062F110F](#)

TE Part # 7-2151080-2
[OCEAN_2.0_APPLICATOR-S-062F110F](#)

TE Part # 7-2151080-7
[OCEAN_2.0_SPARE_PART_KIT-062F110F](#)

Also in the Series | **HDC HD**

Connector Contacts(24)

Insertion & Extraction Tools(5)

Rectangular Contact Inserts(43)

Customers Also Bought



TE Part #1-2299959-1
TRAY PACKAGE.THERMOCOUPLE
CONN KTYPE REC

TE Part #1-2299960-1
TRAY PACKAGE.THERMOCOUPLE
CONN KTYPE TAB

TE Part #2295205-1
THERMOCOUPLE CONNECTOR.
STRAIN RELIEF.

TE Part #2295044-4
RITS CONN. PLUG ASSY 4P YELLOW
TIN

TE Part #T1230240129-000
H24B-TSH-PG29

TE Part #2312733-2
HMN-HD3-10-M

TE Part #2316315-2
HMN-HD1-24-M

TE Part #ASA046N0085050A000
617 PLUG, SPEEDTEC

TE Part #T2113000101-200
HMN-RJ45-M

Documents

Product Drawings

HD3 TAB CONTACT AU0.38 M SIZE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2316815-2_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2316815-2_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2316815-2_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



HEAVY DUTY CONNECTORS

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

English