

Alcoswitch | Alcoswitch PB6

TE Internal #: 2329386-1

Push Button Switches, Single Pole - Single Throw Configuration (Pole-Throw), Switch, Single Actuator, Flush Actuator Profile, Threaded, Alcoswitch PB6

[View on TE.com >](#)

Relays, Contactors &amp; Switches &gt; Switches &gt; Push Button Switches

Configuration (Pole-Throw): **Single Pole - Single Throw**Push Button Switch Product Type: **Switch**Number of Actuators: **Single**Actuator Profile: **Flush**Bushing Style: **Threaded**

## Features

### Product Type Features

Switch Type	Pushbutton
Dust Proof	Yes
Push Button Switch Product Type	Switch
Illuminated	No
Actuator Style	Round

### Configuration Features

ESD Grounding Terminal	Without
Detent Style	Audible
Ganged	No
Configuration (Pole-Throw)	Single Pole - Single Throw
Number of Actuators	Single
Snap Action	Without
Support Bracket	Without
Tactile	No

## Operating Function

Momentary

## Electrical Characteristics

Push Button Switch Voltage Rating

50 VDC

## Body Features

Case Material

Diallyl Phthalate (DAP)

Actuator Material

Polyamide

Actuator Profile

Flush

Bushing Style

Threaded

Bushing Thread Size

M12 x .75

Actuator Color

Black

## Contact Features

Push Button Switch Contact Current Rating

.12 A

Switch Contact Plating Material

Gold over Silver

## Termination Features

Termination Type

Long Leads

## Mechanical Attachment

Mounting Angle

Vertical

Push Button Switch Mounting Type

Panel

## Housing Features

Process Sealed

Yes

## Industry Standards

IP Rating

IP68

## Packaging Features

Packaging Method

Loose Piece

## Other

Comment

(On) indicates momentary position.

## Product Compliance

For compliance documentation, visit the product page on TE.com&gt;

EU RoHS Directive 2011/65/EU

Compliant with Exemptions

EU ELV Directive 2000/53/EC

Compliant with Exemptions

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2023 (235)

Candidate List Declared Against: JUNE 2023 (235)

SVHC &gt; Threshold:

Pb (4% in Component Part)

## Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I &lt; 900 ppm per homogenous material. Also BFR/CFR/PVC Free


Solder Process Capability

Not reviewed for solder process capability

## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


## Compatible Parts



## Also in the Series | Alcoswitch PB6

PB6B2FM2M1CAL00Y500

Push Button Switches, Single Pole - Single Throw Configuration (Pole-Throw), Switch, Single Actuator, Flush Actuator Profile, Threaded, Alcoswitch PB6



Push Button Switches(165)

## Customers Also Bought



TE Part #5787422-1  
HDR ASY,RA,RKEY,STR TAIL,12.0V



TE Part #5530843-3  
CONN SEC II 18 POS 100C/L



TE Part #640389-2  
02P MTA156 HDR ASSY SQ R/A F/L



TE Part #5787526-1  
MDI RECEPTACLE ASSEMBLY,6P




TE Part #5787428-1  
HDR ASY,RA,LKEY,STR TAIL,12.0V



TE Part #2329384-1  
PB OFF/ON FC BLK M1 TERM IP68  
500MM L



TE Part #2329386-4  
PN OFF/ON FC GRE M1 TERM IP68  
500MM LHS



TE Part #5787446-1  
HDR ASY,VERT,NO KEY,RET TAIL



TE Part #1-1414415-0  
RESOLVER V23401-U6119-B609

## Documents

### Product Drawings

[PN OFF/ON FC BLK M1 TERM IP68 500MM LHS](#)

English

### CAD Files

[3D PDF](#)

3D

### Customer View Model

[ENG\\_CVM\\_CVM\\_2329386-1\\_A.2d\\_dxf.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_2329386-1\\_A.3d\\_jgs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_2329386-1\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

**Datasheets & Catalog Pages**

[IP68 Sub Mini PB Data Sheet](#)

English