

# Product data sheet

## Characteristics

# SGA8038

Coded magnetic system, MAGNET SWITCH,  
15 VA, 250 V dc / 130 V ac, 1 A

### Main

Product or Component Type	Coded magnetic system
Contacts type and composition	1 NO
Material	Plastic
Electrical Connection	Pre-cabled
[Ue] rated operational voltage	250 V DC

### Complementary

Protection Type	Overload and short-circuit protection
Breaking capacity	15 VA

### Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...185 °F (-40...85 °C)

### Ordering and shipping details

Category	22487-SENSORS, PROXIMITY, US
Discount Schedule	DS2
GTIN	785901173229
Returnability	No
Country of origin	US

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.30 in (18.542 cm)
Package 1 Width	2.00 in (5.08 cm)
Package 1 Length	7.30 in (18.542 cm)
Package 1 Weight	4.48 oz (127.006 g)

### Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
---------------------------	---

REACH Regulation	 <a href="#">REACH Declaration</a>
------------------	---

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

### Contractual warranty

Warranty	18 months
----------	-----------