

624037-000

✓ ACTIVE


RAYCHEM

TE Internal #: 624037-000

SolderSleeve Shield Terminators, 4.32 mm [.17 in] Expanded Inside, 1.78 mm [.07 in] Recovered Inside, Pre-Installed Lead, 22 AWG Wire Size

[View on TE.com >](#)

Wire Protection & Management > Interconnect Devices > SolderSleeve Shield Terminators



Operating Temperature (Max): 150 °C

Expanded Inside Diameter (Min): 4.32 mm [.17 in]

Recovered Inside Diameter (Max): 1.78 mm [.07 in]

Pre-Installed Lead: Yes

Wire Size: .34 mm²

Features

Configuration Features

Pre-Installed Lead	Yes
--------------------	-----

Dimensions

Expanded Inside Diameter (Min)	4.32 mm [.17 in]
Recovered Inside Diameter (Max)	1.78 mm [.07 in]
Wire Size	22 AWG

Usage Conditions

Operating Temperature (Max)	150 °C
Wire Temperature (Max)	125 °C

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Pb (37% in Solder)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free


Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought



TE Part #878499-000
202K174-25-0




TE Part #359926-000
204W221-25/225-0



TE Part #282096-000
44A0211-22-9



TE Part #216003-005
55A0111-22-4



TE Part #2826933001
44A0211-22-92

Documents

Product Drawings

[D-101-34](#)

English

Datasheets & Catalog Pages

[Raychem Electrical Interconnect Products](#)

English

Product Specifications

Product Specification

English