



Connectors > Power Connectors > Power Contacts



Power Contact Type: **Contact**
Operating Voltage: **250 VDC**
Termination Method to Wire & Cable: **Crimp**
Contact Current Rating (Max): **5 A, 15 A, 35 A, 200 A**

Features

Product Type Features

Power Contact Type	Contact
--------------------	---------

Electrical Characteristics

Operating Voltage	250 VDC
-------------------	---------

Contact Features

Contact Current Rating (Max)	5 A, 15 A, 35 A, 200 A
Contact Type	Pin
Contact Retention Within Housing	With

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

--	--



Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Method	Package
------------------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1648186-1
292-10-01100=SA CONN,SKT



TE Part # 1648601-1
296-22-01100



TE Part # 1650399-1
902-77-02113=SCREW,SHOULDER,10



TE Part # 6643769-1
CONN,SKT,TOP DRAWER



TE Part # 6643765-1
[CONN,SKT,TOP DRAWER](#)

Customers Also Bought



TE Part #9-1393211-4
[T92S11D22-24](#)



TE Part #1879453-1
[TE 1000W 1R0 5% Bracket](#)



TE Part #1648110-1
[221-0010-01100=SA CONN,PIN](#)



TE Part #1648325-1
[702-92-01109=CONTACT,SKT,#20](#)



TE Part #1766194-1
[CONTACT,PIN,#16](#)



TE Part #YDTS20W09-35SNV001
[RECP ASSY](#)



TE Part #YDTS20W15-05PNV001
[RECP ASSY](#)



TE Part #DTS20W25-29SN
[RECP ASSY](#)



TE Part #CZ0325-000
[55A6866-24-9/96CS2621](#)

Documents

Product Drawings

[291-10-01100=SA CONN,PIN](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1648183-1_C.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_1648183-1_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1648183-1_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[POWER_CONNECTORS_CATALOG_SEC02_CABLE_MOUNTED](#)

English

[AMP & ELCON Power Connector Layout Forms Datasheet 6-1773444-7](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[TE Material Declaration](#)

English