




GRACE INERTIA 2.5

TE Internal #: 3-1971793-3  
Housing, Plug, Wire-to-Wire, 3 Position, .098 in [2.5 mm] Centerline,  
Crimp, 1 Row, Red, Mating Retention, Wire & Cable, GRACE  
INERTIA 2.5

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings >  
Glow Wire Sig GRACE INERTIA Plug



Connector Product Type: **Housing**  
Connector & Housing Type: **Plug**  
Connector System: **Wire-to-Wire**  
Number of Positions: **3**  
Centerline (Pitch): **2.5 mm [ .098 in ]**

[All Glow Wire Sig GRACE INERTIA Plug \(20\)](#)

Features

Product Type Features

|                                   |              |
|-----------------------------------|--------------|
| Connector Product Type            | Housing      |
| Connector & Housing Type          | Plug         |
| Connector System                  | Wire-to-Wire |
| Sealable                          | No           |
| Connector & Contact Terminates To | Wire & Cable |

Configuration Features

|                     |   |
|---------------------|---|
| Number of Positions | 3 |
| Number of Rows      | 1 |

Electrical Characteristics

|                   |        |
|-------------------|--------|
| Operating Voltage | 50 VAC |
|-------------------|--------|

Body Features

|  |  |
|--|--|
|  |  |
|--|--|



|                         |   |
|-------------------------|---|
| Connector & Keying Code | C |
|-------------------------|---|

|                       |     |
|-----------------------|-----|
| Primary Product Color | Red |
|-----------------------|-----|

Contact Features

|                                  |         |
|----------------------------------|---------|
| Contact Retention Within Housing | Without |
|----------------------------------|---------|

|                |        |
|----------------|--------|
| Contact Layout | Inline |
|----------------|--------|

|              |     |
|--------------|-----|
| Contact Type | Tab |
|--------------|-----|

|                       |              |
|-----------------------|--------------|
| Contact Base Material | Copper Alloy |
|-----------------------|--------------|

|                              |     |
|------------------------------|-----|
| Contact Current Rating (Max) | 3 A |
|------------------------------|-----|

Termination Features

|                                    |       |
|------------------------------------|-------|
| Termination Method to Wire & Cable | Crimp |
|------------------------------------|-------|

Mechanical Attachment

|               |         |
|---------------|---------|
| Strain Relief | Without |
|---------------|---------|

|                     |         |
|---------------------|---------|
| Panel Mount Feature | Without |
|---------------------|---------|

|                     |         |
|---------------------|---------|
| PCB Mount Retention | Without |
|---------------------|---------|

|                       |       |
|-----------------------|-------|
| Mating Retention Type | Latch |
|-----------------------|-------|

|                  |      |
|------------------|------|
| Mating Retention | With |
|------------------|------|

|                         |                            |
|-------------------------|----------------------------|
| Connector Mounting Type | Cable Mount (Free-Hanging) |
|-------------------------|----------------------------|

Housing Features

|                             |                  |
|-----------------------------|------------------|
| Housing Entry Configuration | Both Ends Closed |
|-----------------------------|------------------|

|                  |          |
|------------------|----------|
| Housing Material | PA 66 GF |
|------------------|----------|

|                    |                 |
|--------------------|-----------------|
| Centerline (Pitch) | 2.5 mm[.098 in] |
|--------------------|-----------------|

Dimensions

|  |         |
|--|---------|
|  | .322 in |
|--|---------|

|                  |                  |
|------------------|------------------|
| Connector Height | 5.88 mm[.231 in] |
|------------------|------------------|

|           |                 |
|-----------|-----------------|
| Wire Size | .081 – .326 mm² |
|-----------|-----------------|

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -30 – 105 °C[-22 – 221 °F] |
|-----------------------------|----------------------------|

Operation/Application

|                     |                |
|---------------------|----------------|
| Circuit Application | Power & Signal |
|---------------------|----------------|

Industry Standards

|                  |           |
|------------------|-----------|
| Glow Wire Rating | Glow Wire |
|------------------|-----------|

|                        |          |
|------------------------|----------|
| UL Flammability Rating | UL 94V-0 |
|------------------------|----------|



Packaging Features

|                    |           |
|--------------------|-----------|
| Packaging Quantity | 400       |
| Packaging Method   | Bag & Box |

Other

|                                 |                         |
|---------------------------------|-------------------------|
| Discrete Wire Connector Comment | Mating with 3-1971798-X |
|---------------------------------|-------------------------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

|   |   |
|---|---|
| EU RoHS Directive 2011/65/EU                  | Compliant   |
| EU ELV Directive 2000/53/EC                   | Compliant   |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold   |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2023 (235)<br>Candidate List Declared Against: JUNE 2023 (235)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.  |
| Solder Process Capability                     | Not reviewed for solder process capability  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # CAT-G7534A-C1701  
STD Temp Sig GRACE INERTIA Cap



TE Part # CAT-G7534A-H342  
STD Temp Sig GRACE INERTIA Header




TE Part # 1903392-1  
GIC 2.5 W CAP HSG 3P NATURAL Header



TE Part # 3-1971794-2  
GI2.5 TPA,3P

Also in the Series | GRACE INERTIA 2.5




Connector Contacts(2)




PCB Headers & Receptacles(138)



PCB Latches, Locks & Retainers(5)




Rectangular Connector Housings(49)




Rectangular Connector Locking(2)



Rectangular Power Connectors(35)



Wire-to-Board Connector Assemblies & Housings(46)



Wire-to-Board Connector Contacts(4)

Customers Also Bought



TE Part #1971795-1  
NEW GI CONN2.5 REC. CONTACT



TE Part #8-1971793-2  
NEW GI CONN2.5 PLUG HSG 8P BLUA



TE Part #1-1393243-5  
RTE24524



TE Part #6-104074-0  
08 SYSTEM 50 HDR SRRA SHRD SN



TE Part #103735-3  
04 MTE HDR SRST LATCH .100CL




TE Part #2129276-1  
PLUG ASSY 0.6mm CHAMP DOCKING



TE Part #2-2213767-1  
AV19 SPL 5A MOVE RING LED WHITE 12V



TE Part #4-1971793-3  
NEW GI CONN2.5 PLUG HSG 4P RED



Documents

Product Drawings

NEW GI CONN2.5 PLUG HSG 3P RED

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_3-1971793-3\_J.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_3-1971793-3\_J.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_3-1971793-3\_J.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

5-1773465-3-GI2.5Flyer

English

7-1773465-8-GI2.5-ChineseFlyer

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English