



Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Strain Relief Cover**

Primary Product Material: **Nylon**

Primary Product Color: **Black**

Number of Positions: **15**

Sealable: **No**

Features

Product Type Features

Strain Relief Accessory Type	Strain Relief Cover
Sealable	No

Configuration Features

Number of Positions	15
---------------------	----

Body Features

Primary Product Material	Nylon
Primary Product Color	Black

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Industry Standards

Agency/Standard	CSA, UL
-----------------	---------

Packaging Features

Packaging Method	Bag
Packaging Quantity	100



Other

Connector Accessory Comment	One piece - Clam Shell.
-----------------------------	-------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



TE Part #205204-9
CRIMP SNAP PLUG ASSY,SIZE 1

TE Part #748364-1
15 HD22 CRIMP SNAP PLUG

TE Part #208493-1
CMC RECEPTACLE ASSY,SIZE 22

TE Part #1-640523-0
15P MR II PLUG HSG V0

TE Part #1-640513-0
15P MR II CAP HSG V0

TE Part #1-640521-0
09P MR II PLUG HSG V0

TE Part #641300-1
MR RECPT PTPHBZ LP 26-18

TE Part #2-34151-1
PG R 22-16 COMM 22-18 MIL 5/16

TE Part #1-350374-9
12P STR/REL HNGD

TE Part #202174-4
GUIDE SOC. ASSY. 104 CTR. FSTN

Documents

Product Drawings

15P MR STR/REL HNG

English

CAD Files

Customer View Model

ENG_CVM_1-350523-9_J.3d_igs.zip

English

Customer View Model

ENG_CVM_1-350523-9_J.3d_stp.zip

English

Customer View Model

ENG_CVM_1-350523-9_J.2d_dxf.zip

English

3D PDF

English

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_1-350523-9_Z.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-350523-9_Z.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-350523-9_Z.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG](#)

English

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[AMP* MINIATURE RECTANGULAR II \(MRII\) CONNECTORS](#)

English