



Connectors > Circular Connectors > Standard Circular Connectors



Sealable: No

Contact Current Rating (Max): 14 A

Circuit Application: Power

Shell Base Material: Brass

Circular Connector Shell Size: 15

Features

Product Type Features

Sealable	No
Shell Type	Metal

Body Features

Shell Base Material	Brass
---------------------	-------

Contact Features

Contact Current Rating (Max)	14 A
Circular Connector Contact Type	Socket

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Housing Features

Circular Connector Shell Size	15
Alignment Keyed	0°

Operation/Application

Durability Rating	500 Cycles
-------------------	------------



Circuit Application

Power

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Pb (1.6% in Component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # ESA205N00330003000
915 PLUG



TE Part # ESA205N00340003000
915 PLUG











TE Part # ESB205N00310003000
915 PLUG













TE Part # ESB205N00330003000
915 PLUG



 <p>TE Part # C0-0201-000-000 CRIMPING TOOL MID-SIZE</p>	 <p>TE Part # C0-0235-000-000 DIGITAL CRIMPING TOOL, SMALL</p>	 <p>TE Part # C0-0258-000-000 POSITIONING INSERT FOR 1 MM CONTACTS</p>	 <p>TE Part # ESA202F01320500000 915 PLUG</p>
 <p>TE Part # ESA202F01340500000 915 PLUG</p>	 <p>TE Part # ESA205N00310003000 915 plug</p>	 <p>TE Part # ESA205N00320003000 915 PLUG</p>	 <p>TE Part # ESB205N00320003000 915 PLUG</p>

Customers Also Bought

 <p>TE Part #60-0216-011-000 CONTACT SOCKET 1 MM</p>	 <p>TE Part #ASA020F11620235000 623 PLUG</p>	 <p>TE Part #BSA078N00590100000 923 PLUG, SPEEDTEC</p>	 <p>TE Part #ESA202N00330500000 915 PLUG</p>
 <p>TE Part #10-0525-002-000 623 PLUG HOUSING IG3</p>	 <p>TE Part #10-0723-002-000 923 PLUG HOUSING IG3, SHORT</p>	 <p>TE Part #40-0985-000-000 623 INSULATION INSERT, 12-PIN</p>	 <p>TE Part #40-A486-000-000 406 ETHERNET ELEMENT CAT 5</p>
 <p>TE Part #ESA202N00320500000 915 PLUG</p>	 <p>TE Part #HEC011N00000300000 723 HTEC RECEPTACLE, SPEEDTEC</p>		

Documents



Product Drawings

CONTACT SOCKET 1 MM

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_60-0251-011-000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_60-0251-011-000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_60-0251-011-000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Socket 1mm 60.251.11

English