



Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Cover**

Cable Entry Location: **Bottom**

Hood & Base Locking Device Type: **Locking**

Sealable: **Yes**

Circuit Application: **Power & Signal**

Features

Product Type Features

Hood & Base Connector Product Type	Cover
Sealable	Yes

Body Features

Cable Entry Location	Bottom
----------------------	--------

Mechanical Attachment

Locking Device Location	Housing
Hood & Base Locking Device Type	Locking

Dimensions

Product Width	24 mm
Product Length	24 mm

Usage Conditions

Corrosion Protected	Yes
---------------------	-----

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Method	Box
------------------	-----



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # T1619031111-000
H3A-AGSV-PG11



TE Part # T1509030500-000
H3A-MAG





TE Part # T1509030000-000
H3A-MAG



TE Part # T1549030000-000
H3A-MAGS



 TE Part # T1509031000-000 H3A-MAG-S	 TE Part # T1509031100-000 H3A-AG	 TE Part # T1506033000-000 H3A-MAG-EMC	 TE Part # T1509031111-000 H3A-AGS
 TE Part # T1619030111-000 H3A-MAGSV-PG11	 TE Part # T1619030116-000 H3A-MAGSV-M16	 TE Part # T1619030120-000 H3A-MAGSV-M20	 TE Part # T1739030111-000 H3A-MTGVB-PG11
 TE Part # T1739030120-000 H3A-MTGVB-M20	 TE Part # T1739035120-000 H3A-MTGVB-M20-EMC	 TE Part # T1509033120-000 H3A-MAG-M20	 TE Part # T1739032120-000 H3A-TGVB-M20
 TE Part # T1739032111-000 H3A-TGVB-PG11	 TE Part # T1509033111-000 H3A-MAG-PG11	 TE Part # T1546033000-000 H3A-MAGS-EMC	 TE Part # T1619031116-000 H3A-AGSV-M16

Also in the Series | [HDC IP65](#)



Rectangular Connector Hoods & Bases
(1258)

Customers Also Bought





TE Part #T1310160125-000
H16B-TS-RO-M25



TE Part #T2040102101-000
HE-010-M



TE Part #T1549030000-000
H3A-MAGS



TE Part #T2010032101-000
HA-003-M



TE Part #T2010043201-000
HA-004-FS



TE Part #T2010032201-000
HA-003-F



TE Part #T1230240121-000
H24B-TSH-PG21



TE Part #T2040322101-000
HE-016-M 17-32



TE Part #T2040242201-000
HE-024-F



TE Part #T1329030111-000
H3A-MTG-PG11

Documents

Product Drawings
H3A-KDBP-NY150

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_T1010032100-000_A.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_T1010032100-000_A.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_T1010032100-000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



Heavy Duty Connectors

English

HEAVY DUTY CONNECTORS

English

Product Specifications

Application Specification

English