




Connectors > Modular Jacks & Plugs > Modular Jack & Plug Accessories > Modular Jack & Plug Caps & Covers



Connector Cover Type: **Protective Cover**

Sealable: **Yes**

Operating Temperature Range: **-40 – 85 °C [ -40 – 185 °F ]**

Features

Product Type Features

Closure Cap Type	Plug Cordset
Connector Cover Type	Protective Cover
Sealable	Yes

Body Features

Primary Product Material	Polyester
Seal Material	Silicone Rubber

Mechanical Attachment

Component Retention Feature	Lanyard
-----------------------------	---------

Housing Features

Compatible With Connector Shape	Circular
---------------------------------	----------

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Packaging Features

Packaging Quantity	1
Packaging Method	Bag, Box

Other

--	--



Coupling Nut Base Material	Zinc
Lanyard Length	127 mm[5 in]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts













TE Part # 1954643-1  
Recpt Kit, Series A to Series A



TE Part # 2355443-2  
RJ45 CAT5e PANEL MOUNT SOCKET (PBT)

Customers Also Bought



 <p>TE Part #1828619-1 Kit, Receptacle, LC, ODVA, MM</p>	 <p>TE Part #1776293-3 TSB23003DS=EUROPA TERM BLK, 8MM</p>	 <p>TE Part #66262-4 MALE CONTACT ASSY. (L.P.)</p>	 <p>TE Part #1445336-3 LOOSE PC CONTACT 30 AU PLATED</p>
 <p>TE Part #1776293-8 TSB23008DS=EUROPA TERM BLK, 8MM</p>	 <p>TE Part #2362760-2 IDC PLUG, PBT</p>	 <p>TE Part #5650187-1 CONN SEC II 17 POS 100 C/L R/A</p>	 <p>TE Part #EH9502-000 PC4D0024BT-19NX-1-C</p>
 <p>TE Part #4-1768602-6 LBC-13030</p>	 <p>TE Part #2029173-6 6P VRT HDR VAL-U-LOK V0 W/ODH</p>		

Documents

Product Drawings  
RJ45 PROTECTION CAP (PBT)

English

CAD Files

3D PDF

3D

Customer View Model  
ENG\_CVM\_CVM\_2355444-2\_B.2d\_dxf.zip

English

Customer View Model  
ENG\_CVM\_CVM\_2355444-2\_B.3d\_igs.zip

English

Customer View Model  
ENG\_CVM\_CVM\_2355444-2\_B.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications



Application Specification

English

Product Environmental Compliance

Product Compliance Document

English

Product Compliance Document

English