




MATE-N-LOK | Universal MATE-N-LOK

TE Internal #: 926305-6
Rectangular Power Connectors, Housing, Receptacle, Wire-to-Wire / Wire-to-Panel, 4 Position, 6.35 mm [.25 in] Centerline, Universal MATE-N-LOK

[View on TE.com >](#)

Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**
Connector & Housing Type: **Receptacle**
Connector System: **Wire-to-Panel, Wire-to-Wire**
Number of Positions: **4**
Centerline (Pitch): **6.35 mm [.25 in]**

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Panel, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
Number of Power Positions	0
Number of Signal Positions	0
Number of Rows	1

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features

Multiple Contact Types	Without
------------------------	---------



Contact Layout	Inline
Contact Retention Within Housing	Without
Contact Type	Pin

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Panel Mount Feature	With
Panel Mount Feature Type	Latches
Connector Mounting Type	Panel Mount

Housing Features

Centerline (Pitch)	6.35 mm[.25 in]
Housing Color	Natural
Housing Material	PA 6

Dimensions

Panel Thickness (Recommended)	.76 – 2.29 mm[.03 – .09 in]
-------------------------------	-----------------------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

CSA Rating	Certified, LR 7189
UL Rating	Recognized
Agency/Standard	CSA, UL, VDE
Approved Standards	UL E28476
UL Flammability Rating	UL 94V-2
Glow Wire Rating	GWT 750°C (Without Flame)

Packaging Features

Packaging Quantity	2000
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 350793-1 04P UMNL PIN HDR ASSY 94VO	 TE Part # 350430-4 04P UMNL PIN HDR ASSY NATL LF	 TE Part # 350826-4 04P UMNL HDR ASSY PC 94VO LF	 TE Part # 350833-1 04P UMNL HDR ASSY PC 94VO
 TE Part # 173926-1 4 P ACTION PIN UMNL	 TE Part # 350761-5 04P UMNL HDR ASSY PC LF	 TE Part # 350793-3 04P UMNL PIN HDR ASSY 94VO LF	 TE Part # 770019-1 04P UMNLI IN-LNE PLUG HSG KIT



 TE Part # 350430-1 04P UMNL PIN HDR ASSY NATL	 TE Part # 350779-4 04P UMNL PLUG HSG UL94VO	 TE Part # 1-350944-0 04P UMNL HDR ASSY R/A 94VO	 TE Part # 350792-1 04P UMML PIN HDR ASSY 94VO
 TE Part # 641968-1 04P UMNL PIN HDR ASSY POL 94VO	 TE Part # 643415-1 04P UMNL HDR ASSY POL	 TE Part # 926298-3 04P UNIV.M-N-L.PLUG	 TE Part # 2-480702-0 04P UMNL PLUG HSG NATL
 TE Part # 350826-1 04P UMNL HDR ASSY PC 94VO	 TE Part # 643230-1 04P UMNL HDR ASSY R/A 94VO	 TE Part # 926298-6 UNML PLUG 4WAY	 TE Part # 350779-1 04P UMNL PLUG HSG

Also in the Series | Universal MATE-N-LOK

 Circular Power Connectors(2)	 Connector Contacts(2)	 Connector Seals & Cavity Plugs(27)	 Connector Strain Relief(34)
 Insertion & Extraction Tools(4)	 Power Contacts(207)	 Rectangular Connector Adapters(7)	 Rectangular Connector Hardware(1)



Rectangular Connector Housings(1)



Rectangular Connector Keying Plugs(3)



Rectangular Connector Locking(8)




Rectangular Power Connectors(672)

Customers Also Bought



TE Part #1-1879234-9
SMF5 3K0 5%



TE Part #87631-5
10 MODIV HSG COMP DR .100 POL



TE Part #926298-3
04P UNIV.M-N-L.PLUG



TE Part #1586845-1
04P UMNL CAP HSG NATL, GW



TE Part #640586-1
08P UMNL PLUG HSG V2 NATL



TE Part #926299-5
UNML PLUG 5WAY



TE Part #926882-3
UMNL SOK PTPPHBZ



TE Part #2-480703-0
04P UMNL CAP HSG NATL



TE Part #58530-1
AMP PRO-CRIMPER HAND TOOL II

Documents

Product Drawings

UNML4WAY CAP

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_926305-6_H.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_926305-6_H.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_926305-6_H.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[2_PIECE_POWER_CONNECTORS_qrg_4-1773458-1](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English

Agency Approvals

[VDE Certificate](#)

English