




RAST | RAST 5D

TE Internal #: 964203-2

Automotive Terminals, Receptacle, Mating Tab Width 5.8 mm [.228 in], Tab Thickness .8 mm [.031 in], 17 – 13 AWG Wire Size, RAST 5D

[View on TE.com >](#)

Terminals & Splices > Automotive Terminals



Terminal Type: **Receptacle**
Mating Tab Width: **5.8 mm [.228 in]**
Mating Tab Thickness: **.8 mm [.031 in]**
Terminal Transmits: **0 – 24 A (Low Power)**
Wire Size: **17 – 13 AWG**

Features

Product Type Features

Sealable	No
Primary Locking Feature	Locking Lance

Contact Features

Contact Size	6.3mm
Contact Fabrication	Stamped & Formed
Crimp Type	F-Crimp
Terminal Type	Receptacle
Mating Tab Width	5.8 mm[.228 in]
Mating Tab Thickness	.8 mm[.031 in]
Interface Plating	Tin (Sn)

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

Dimensions

--	--



Wire Size	1 – 2.5 mm²
Wire Size Search	13 AWG, 14 AWG, 15 AWG, 16 AWG, 17 AWG

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C, 140 °C[176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F][284 °F]
Operating Temperature Range	-40 – 140 °C[-40 – 284 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Packaging Features

Packaging Quantity	2300
Packaging Method	Reel

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products



will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 4-1579007-3 EXTRACTION TOOL KIT	 TE Part # 1-1579007-6 EXTRACTION TOOL	 TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp	 TE Part # 1241959-4 STD-TIM HSG MKII 4P
 TE Part # 1-2178571-3 STANDARD TIMER HSG 3P	 TE Part # 1-2315717-2 STD TIMER PLUG HSG 2P MKII	 TE Part # 2-2151059-1 OCEAN_2.0_APPLICATOR-S-110F140OV	 TE Part # 2-2151059-2 OCEAN_2.0_APPLICATOR-S-110F140OV
 TE Part # 2-2315717-2 STD TIMER PLUG HSG 2P MKII	 TE Part # 2151059-1 OCEAN_2.0_APPLICATOR-S-110F140OV	 TE Part # 2151059-2 OCEAN_2.0_APPLICATOR-S-110F140OV	 TE Part # 7-2151059-1 OCEAN_2.0_APPLICATOR-S-110F140OV
 TE Part # 7-2151059-2 OCEAN_2.0_APPLICATOR-S-110F140OV	 KIT TE Part # 7-2151059-7 OCEAN_2.0_SPARE_PART_KIT-110F140OV		

Also in the Series | RAST 5D




Automotive Terminals(5)



Connector Contacts(10)



Insertion & Extraction Tools(1)



PCB Headers & Receptacles(69)



Wire-to-Board Connector Assemblies & Housings(88)

Customers Also Bought



TE Part #794617-6
6POS,MICRO MNL,RCPT HSG




TE Part #104257-3
04 MTE RCPT HSG SR LATCH .100




TE Part #350777-4
02P UMNL PLUG HSG UL94V0




TE Part #964203-5
STD PW TIMER CONTACT



TE Part #62336-1
110 FASTON FLAG REC 22-18 AWG TPBR



TE Part #5-160432-4
250 FASTON REC 20-16 AWG TPBR




TE Part #2-520334-2
ULTRAFast 187 ASSY FLAG REC 22-18 TPBR



TE Part #964971-1
EINZELLEITERDICHTNG



TE Part #323152
DG 22-16COM 22-18MIL HR R 8



TE Part #969005-2
MT2 A REC 1.6 Contact SWS Sn

Documents



Product Drawings

STD PW TIMER CONTACT

English

CAD Files

Customer View Model

ENG_CVM_964203-2_C.3d_igs.zip

English

Customer View Model

ENG_CVM_964203-2_C.3d_stp.zip

English

Customer View Model

ENG_CVM_964203-2_C.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

German

Application Specification

English

Application Specification

English