

Applicable standard		Specifications								
Rating 	Operating Temperature Range	-55 to +105°C (Note1)		Storage Temperature Range	-10 °C to +60°C (Note3)					
	Operating Humidity Range	20% to 80% (Note2)		Storage Humidity Range	40% to 70% (Note3)					
	Applicable Connector	DF51A-6P-2DSA/DS(##) DF51-6EP-2C(##)		Current	AWG 22 to 26 : 2.0A AWG 28 : 1.0A AWG 30 : 0.5A					
	Applicable Contact	DF11-22SC(A)/SCF(A) DF11-2428SC(A)/SCF(A) DF11-30SC(A)/SCF(A)			30 V AC/DC					
	Voltage	250 V AC/DC		UL • C-UL Rating	AWG 22 : 2.0A AWG 24 to 28 : 1.0A AWG 30 : 0.5A					
Construction										
General Examination	Visually and by measuring instrument.		According to drawing.		X X					
Marking	Confirmed visually.				X X					
Electric Characteristics 										
Insulation Resistance	500 V DC.		1000 MΩ MIN.		X —					
Voltage Proof	650 V AC for 1 min.		No flashover or breakdown.		X —					
Mechanical Characteristics										
Mechanical Operation (Sn Plating)	30 times insertion and extraction.		No damage, crack or looseness of parts. 		X —					
Mechanical Operation (Au Plating)	50 times insertion and extraction.				X —					
Mating and unmating Force (Sn Plating)	It takes out and inserts with a conformity connector.		1.Insertion Force : 38.0N MAX. 2.Extraction Force : 1.5N MIN.		X —					
Mating and unmating Force (Au Plating)	It takes out and inserts with a conformity connector.		1.Insertion Force : 29.7N MAX. 2.Extraction Force : 1.5N MIN.		X —					
Vibration	Frequency 10 to 55 Hz, single amplitude 0.75 mm, at 10 cycles for 3 direction.		No damage, crack or looseness of parts. 		X —					
Shock	Acceleration 490 m/s ² duration of pulse 11 ms at 3 times for 3 directions.				X —					
Contact extraction force	Pull out the cable after housing fixation.		11.8N MIN		X —					
Environmental Characteristics										
Damp Heat (Steady State)	Exposed at 40 ± 2°C, humidity 90 to 95 %, 96 h. (After leaving the room temperature for 1 to 2h.)		1.Insulation resistance: 500 MΩ MIN. 2.No damage, crack or looseness of parts. 		X —					
Rapid Change Of Temperature	Temperature -55°C → +105°C Time 30min → 30min Under 5 Cycles. (The transferring time of the tank is 2 to 3 MIN) (After leaving the room temperature for 1 to 2h.)		1.Insulation resistance: 1000 MΩ MIN. 2.No damage, crack or looseness of parts. 		X —					
Dry Heat	Exposed at 105 ± 2°C, 96h				X —					
Cold	Exposed at -55 ± 3°C, 96h				X —					
Remarks										
Note 1:Include the temperature rising by current.										
Note 2:No condensing										
Note 3:Apply to the condition of long term storage for unused products before mount on pcb, After mounted on pcb, operating temperature and humidity range is applied for interim storage during transportation.										
COUNT		DESCRIPTION OF REVISIONS		DESIGNED	CHECKED					
 6		DIS-H-00004567		TS. MIYAKI	SZ. ONO					
				APPROVED	HS. OKAWA					
				CHECKED	YN. TAKASHITA					
				DESIGNED	TT. OHSAKO					
Unless otherwise specified, refer to IEC 60512.				DRAWN	TT. OHSAKO					
Note QT:Qualification Test AT:Assurance Test X:Applicable Test				DRAWING NO.						
	SPECIFICATION SHEET		PART NO.	DF51-6S-2C						
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL543-5124-0-00						
					 1/1					