




EMI & EMC Solutions > EMI Filters > Multi-Function Inlet Filters > IEC Filtered Inlets, Corcom SRB Series



Filter Type: **Power Line**
Product Orientation: **Vertical**
Leakage Current (Max) (120VAC, 60Hz): **160 μ A**
Leakage Current (Max) (250VAC, 50Hz): **280 μ A**
Current Rating: **20 A**

[All IEC Filtered Inlets, Corcom SRB Series \(71\)](#)

Features

Product Type Features

Ground Choke Option	No
Filter Type	Power Line
Output Termination Type	Wire Lead
Filtering Requirements	Filtered
Filter Connector Type	IEC 60320-1 C-20

Electrical Characteristics

Leakage Current (Max) (120VAC, 60Hz)	160 μ A
Leakage Current (Max) (250VAC, 50Hz)	280 μ A
Current Rating	20 A
Operating Voltage	250 VAC

Body Features

Product Orientation	Vertical
---------------------	----------



Mechanical Attachment

Panel Mount Feature Type	Flanged
--------------------------	---------

Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

Other

EMI Filters Comment	14 AWG Output Wire
---------------------	--------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-C8114-SR15
IEC Filtered Inlets, Corcom SRB Series

TE Part # 5-1609152-4
20SRB1-W=F8427

Also in the Series | Corcom SRB

Multi-Function Inlet Filters(78)

Customers Also Bought

TE Part #1658643-1
HDP-20,RCPT,SIZE 1, 9 POSN,CLI

TE Part #6-6609107-2
PS0S0SSXB=C1121

TE Part #1658538-1
SOCKET CONT DUPL PLT LP HD-20

TE Part #5650461-5
ASSY,RECEPTACLE,EUROCARD,TYPE

TE Part #102387-1
10 MODIV HSG COMP DR .100 POL

TE Part #2-520409-2
ULTRA-FAST 187 ASY REC 22-18 TPBR

TE Part #62003-1
110 FASTON REC 22-16 AWG BR

TE Part #6-87756-8
MOD IV RECP LP

TE Part #2176326-7
CRGP 0603 33R 1%

TE Part #2-2176307-8
RP 1E 0.1W 23K7 0.1% 25PPM 5K RL



Documents

Product Drawings

20SRB8-Y=F8431

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-1609152-8_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5-1609152-8_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-1609152-8_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1654001_CORCOM_PRODUCT_GUIDE

English

Corcom 20SRB Series Flyer

English

Corcom Combined Selector Charts

English