




Connectors > PCB Connectors > PCB Headers & Receptacles



Connector System: **Wire-to-Board**  
Number of Positions: **10**  
Number of Rows: **1**  
Centerline (Pitch): **5 mm [.197 in]**  
PCB Mount Orientation: **Vertical**

Features

Product Type Features

Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
PCB Connector Assembly Type	PCB Mount Header

Configuration Features

Number of Columns	10
Number of Loaded Positions	10
Connector Contact Load Condition	Fully Loaded
Number of Positions	10
Number of Rows	1
PCB Mount Orientation	Vertical

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------



Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

PCB Contact Termination Area Plating Material Thickness	3.81 μm[150 μin]
Mating Pin Diameter	1.75 mm[.069 in]
Contact Underplating Material Thickness	1.27 μm[50 μin]
Contact Mating Area Plating Material Thickness	3.81 μm[150 μin]
PCB Contact Termination Area Plating Material Finish	Matte
Contact Mating Area Plating Material Finish	Matte
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Tin
Contact Type	Pin
Contact Current Rating (Max)	7.5 A

Termination Features

Round Termination Post & Tail Diameter	.99 mm[.039 in]
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

Mating Alignment Type	Polarization
Mating Retention	With
PCB Mount Retention Type	Screw Mount
Connector Mounting Type	Board Mount
Mating Alignment	With
PCB Mount Alignment	Without
PCB Mount Retention	With

Housing Features

Housing Material	PA 66
Centerline (Pitch)	5 mm[.197 in]

Usage Conditions

Operating Temperature Range	-55 – 130 °C[-67 – 266 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------



Industry Standards

Agency/Standard	CSA, UL, VDE
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Type	Tube
----------------	------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 207396-1  
HSG,PLUG 10 POSN,METRIMATE

TE Part # 207397-1  
HSG,RECEPT 10 POSN,METRIMATE

Also in the Series | AMP Metrimate

Connector Strain Relief(5)

PCB Headers & Receptacles(83)

Rectangular Connector Hardware(3)

Rectangular Connector Housings(35)

Rectangular Connector Keying Plugs(1)

Rectangular Contact Inserts(4)

Rectangular Power Connectors(2)

Standard Rectangular Connectors(5)

Customers Also Bought

TE Part #66181-1  
III+ SKT,SOLDER,30AU,10AU FLASH,LP

TE Part #DTM06-12SA-E003  
PLG, 12P, GRY, N, CAP, A

TE Part #350550-1  
UMNL SOK 20-14 PTPBR L/P

TE Part #1586851-1  
02P UMNL PLUG HSG, GW

TE Part #1-1879208-5  
CPF 0402 39R 0.1% 25PPM 1K RL

TE Part #1623750-6  
ER58 15K 5% AMMO

TE Part #6-1393254-1  
W92-X1110-10=M6/M7/M9/W6/W7

TE Part #1-2176305-7  
RP 1E 0.1W 158R 0.1% 25PPM 5K RL



Documents

Product Drawings

METRIMATE PIN HEADER ASSY,10P

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_207398-6\_T.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_207398-6\_T.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_207398-6\_T.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

METRIMATE\_PIN\_SOCKET\_CATALOG

English

Product Specifications

Application Specification

English

METRIMATE Self-Locking Connectors

Japanese

Application Specification

Japanese

Product Environmental Compliance

MD\_207398-6\_09272012137

English

MD\_207398-6\_09272012137

English



[Agency Approvals](#)

[CSA Certificate](#)

English