



Connectors > Circular Connectors > Standard Circular Connectors



Sealable: No

Contact Current Rating (Max): 30 A

Circuit Application: Power

Shell Base Material: Brass

Circular Connector Shell Size: 40

Features

Product Type Features

Sealable	No
Shell Type	Metal

Body Features

Shell Base Material	Brass
---------------------	-------

Contact Features

Contact Current Rating (Max)	30 A
Circular Connector Contact Type	Pin

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Housing Features

Circular Connector Shell Size	40
Alignment Keyed	0°

Operation/Application

Durability Rating	500 Cycles
-------------------	------------



Circuit Application

Power

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2023 (233) SVHC > Threshold: Pb (1.5% in Component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # C0-0008-000-000 CRIMPING TOOL LARGE	 TE Part # C0-0247-000-000 POSITIONING INSERT FOR 3.6 MM CONTACTS	 TE Part # C0-0313-000-000 CRIMPING DEVICE HC20 IN CASE
--	--	---

Customers Also Bought



 TE Part #61-0193-011-000 CONTACT PIN 2 MM	 TE Part #61-0195-011-000 CONTACT PIN 3.6 MM	 TE Part #61-0216-011-000 CONTACT PIN 2 MM	 TE Part #BSA078F05420100000 923 PLUG, SPEEDTEC
 TE Part #CGE271N00000051000 940 RECEPTACLE ANGLED, ROTATABLE, SP-READY	 TE Part #22-0127-035-000 940 RECEPTACLE, ANGLED, SPEEDTEC	 TE Part #40-B198-000-000 917 ISO-E TS 10POS DSUB	 TE Part #61-0373-081-000 BAND PIN 2.0 CRIMP 0.25 - 0.75
 TE Part #81-0006-090-000 O-RING 18 X 1,5	 TE Part #D1-0134-041-000 COUNTERSUNK SCREW TT2K M3 X 10		

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_61-0196-011-000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_61-0196-011-000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_61-0196-011-000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Contact Pin 3.6 mm 61-0196-011-000

English