



Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Melamine (3% in Component Part) Article Safe Usage Statements: Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




Compatible Parts



TE Part # 1-626040-0
RELY BASE MOLDING 5W
POLYPROPYLENE



TE Part # 176986-1
FF 250 PLUG HSG 1P NYLON NAT




TE Part # 178024-7
FF 250 CAP HSG DBL 6P PLATE


Customers Also Bought



TE Part #342183-1
12-10 F.E.P.G. RING TONGUE 3BA




TE Part #MS560702BA03-50
MS5607-02BA SS CAP ALTIMETER T&R



TE Part #154718-3
PL 250 REC 0.7-2.0 MM2 0.406 TPBR




TE Part #170342-2
250 FASTON,REC.,20-14 AWG,TPBR



TE Part #60932-2
SPLICE 2500-4700 .020 TPST



TE Part #2-36451-1
TERMINAL,SOLIS R 12-10 10



TE Part #MS583702BA01-50
MS5837-02BA01 2BA T&R PRESSURE
SEN



TE Part #2-1747066-6
GRACE INERTIA CONN 2.5 PLUG
HSG 6P BLUE



TE Part #4-1971030-5
5POS PLUG HOUSING FOR GIC 2.0
EV SERIES



TE Part #2822993001
44A0211-8-0

Documents

Product Drawings
250 FASTON HSG. REC 2P NATURAL
English

CAD Files
Customer View Model
ENG_CVM_CVM_1-172130-1_D.3d_igs.zip
English



Customer View Model

[ENG_CVM_CVM_1-172130-1_D.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-172130-1_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

[Datasheets & Catalog Pages](#)

[White Paper: Nylon Discoloration](#)

English

[Product Specifications](#)

[Application Specification](#)

English

[Product Environmental Compliance](#)

[Product Compliance](#)

English

[Product Compliance](#)

English

[Agency Approvals](#)

[CSA Certificate](#)

English

[CSA Certificate](#)

English