




GRACE INERTIA 7.92

TE Internal #: 1-1747052-5

Rectangular Power Connectors, Header, Receptacle, Wire-to-Board, 2 Position, 7.92 mm [.312 in] Centerline, Printed Circuit Board, GRACE INERTIA 7.92

[View on TE.com >](#)

Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Header**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **2**

Centerline (Pitch): **7.92 mm [.312 in]**

Features

Product Type Features

Header Type	Fully Shrouded
Rectangular Power Connector Type	Header
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	2
PCB Mount Orientation	Vertical
Number of Power Positions	2
Number of Signal Positions	2
Number of Rows	1

Electrical Characteristics

Operating Voltage	300 VDC
-------------------	---------



Contact Features

Contact Mating Area Plating Material	Tin
Contact Current Rating (Max)	10 A
Contact Retention Within Housing	With
Contact Type	Tab
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	1 µm[39.37 µin]

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
---	-----------------------

Mechanical Attachment

PCB Mount Alignment Type	Locating Posts
Mating Retention	With
PCB Mount Alignment	With
PCB Mount Retention	With
PCB Mount Retention Type	Kinked
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	7.92 mm[.312 in]
Housing Color	Green
Housing Material	Nylon 6/6 GF

Dimensions

Wire Size	434.18 – 2723.46 CMA
-----------	----------------------

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	GWT 750°C (Without Flame)

Packaging Features

Packaging Method	Bag
------------------	-----



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 1747052-5
GRACE INERTIA CONNECTOR 7.92 2POS HEADER



TE Part # 1747052-2
GIC7.92 2POS_HEADER ASS'Y RED KEYING A






TE Part # 1747052-3
GIC7.92 2POS_HEADER ASSY BLUE



TE Part # 2-1747052-2
GIC7.92 2POS_HDR ASS'Y RED KEYING C



 TE Part # 3-1747052-2 GIC7.92 2POS_HDR ASS'Y RED KEYING D	 TE Part # 1747052-4 GIC7.92 2POS_HEADER ASS'Y YELLO KEYING A	 TE Part # 3-1747052-1 GIC7.92 2POS_HDR ASS'Y NAT KEYING D	 TE Part # 2-1747052-5 GIC7.92 2POS_HDR ASS'Y GREEN KEYING C
 TE Part # 1-1747052-1 GIC7.92 2POS_HEADER ASS'Y NAT KEYING B	 TE Part # 1-1747052-3 GIC7.92 2POS_HEADER ASS'Y BLUE KEYING B	 TE Part # 1-1747052-4 GIC7.92 2POS_HDR ASS'Y YELLOW KEYING B	 TE Part # 1-2232784-2 GIC 7.92MM CONN HDR ASS'Y 2POS RED
 TE Part # 2-1747052-1 GIC7.92 2POS_HDR ASS'Y NAT KEYING C	 TE Part # 2-1747052-4 GIC7.92 2POS_HDR ASS'Y YELLOW KEYING C	 TE Part # 3-1747052-3 GIC7.92 2POS_HDR ASS'Y BLUE KEYING D	 TE Part # 3-1747052-5 GIC7.92 2POS_HDR ASS'Y GREEN KEYING D
 TE Part # 1-2232784-1 GIC7.92 2POS_HEADER ASS'Y NAT KEYING B			

Also in the Series | GRACE INERTIA 7.92


 Rectangular Power Connectors(39)

Customers Also Bought






TE Part #5-1971798-3
NEW GI CONN2.5 HDR ASMBLY 5P
RED D1.0



TE Part #1-1747052-2
GIC 7.92MM CONN HDR ASS'Y 2POS
RED




TE Part #2-1747052-2
GIC7.92 2POS_HDR ASS'Y RED
KEYING C



TE Part #3-1747052-1
GIC7.92 2POS_HDR ASS'Y NAT
KEYING D



TE Part #1-1747052-1
GIC7.92 2POS_HEADER ASS'Y NAT
KEYING B



TE Part #1-1747052-3
GIC7.92 2POS_HEADER ASS'Y BLUE
KEYING B



TE Part #1-1747052-4
GIC7.92 2POS_HDR ASS'Y YELLOW
KEYING B



TE Part #1871843-5
GIC2.5 HDR ASSY TIN VERSION 5P
NATURAL



TE Part #2-2360545-4
SGI 1.5 HDR, 4P, RA, Key B, Black



TE Part #1-2328608-7
7P, RAST 5 TAB HEADER, THV,
SHORT PEG

Documents

Product Drawings
GIC7.92 2POS_HDR ASS'Y GREEN KEYING B
English

CAD Files
Customer View Model
ENG_CVM_CVM_1-1747052-5_F.2d_dxf.zip
English
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1-1747052-5_F.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_1-1747052-5_F.3d_stp.zip
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



5.0 POWER KEY CONNECTOR

Japanese

Application Specification

Japanese

Product Environmental Compliance

Product Compliance

English

Product Compliance

English