



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Connector & Housing Type: **Receptacle**
Number of Positions: **4**
Terminal Orientation: **Straight**
UL Flammability Rating: **UL 94V-2**

Features

Product Type Features

Sealable	No
Connector & Contact Terminates To	Wire & Cable
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	4
---------------------	---

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	Without

Mechanical Attachment

Mating Alignment Type	Polarization
-----------------------	--------------



Mating Alignment	With
Housing Features	
Housing Material	Nylon
Centerline (Pitch)	5 mm[.2 in]
Dimensions	
Product Length	18 mm[.71 in]
Usage Conditions	
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
Industry Standards	
UL Flammability Rating	UL 94V-2
Packaging Features	
Packaging Quantity	5000

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 926728-1
FF 110 REC HSG 4P NYLON BLACK

TE Part # 968864-1
FF 110 REC HSG 2P NYLON NAT

Also in the Series | FASTIN-FASTON 110

Automotive Housings(6)

Automotive Terminals(6)

Crimp Terminal Housings(34)

Insertion & Extraction Tools(3)

Quick Disconnects(83)

Customers Also Bought

TE Part #1-962349-1
6P STIFT-GEH 3MM

TE Part #D761993001
RAY-101-10.0(100)


TE Part #5-1419168-8
2X8 SEALD HARN ASSY W/CPA

TE Part #1-1534840-1
12POS MQS TAB COD A






TE Part #2822344-1
MINI MLC CAP HSG ASSY 7P



TE Part #185028-1
TAB F 2.8x0.8 CONTACT CS SWS Sn



TE Part #2-160967-2
CABLE TY 98X2.5 BLA



TE Part #150572-2
MINI FASTON 110 REC 20-16 AWG TPBR



TE Part #965383-1
MQS SICHERGSCHIEBER 8POS

TE Part #925014
2 P FF 110(2.8 MM) HOUSING RECEPTACLE

Documents

Product Drawings

4P FF .110 HOUSING REC PA66 NATURAL

English

CAD Files

Customer View Model

ENG_CVM_CVM_925016_E.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_925016_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_925016_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

FASTIN_FASTON_Product_Line

English

White Paper: Nylon Discoloration

English

Product Specifications

Application Specification

English



Product Environmental Compliance

Product Compliance Document

English

Product Compliance Document

English