



Connectors > PCB Connectors > PCB Headers & Receptacles



Connector System: **Wire-to-Board**

Number of Positions: **16**

Number of Rows: **1**

Centerline (Pitch): **2.54 mm [.1 in]**

PCB Mount Orientation: **Right Angle**

Features

Product Type Features

|                                   |                       |
|-----------------------------------|-----------------------|
| Connector System                  | Wire-to-Board         |
| Header Type                       | Fully Shrouded        |
| Sealable                          | No                    |
| Connector & Contact Terminates To | Printed Circuit Board |
| PCB Connector Assembly Type       | PCB Mount Header      |

Configuration Features

|                       |             |
|-----------------------|-------------|
| Number of Positions   | 16          |
| Number of Rows        | 1           |
| PCB Mount Orientation | Right Angle |

Electrical Characteristics

|                                       |         |
|---------------------------------------|---------|
| Termination Resistance                | 15 mΩ   |
| Insulation Resistance                 | 5000 MΩ |
| Dielectric Withstanding Voltage (Max) | 600 V   |

Body Features

|                       |       |
|-----------------------|-------|
| Primary Product Color | Black |
|-----------------------|-------|

Contact Features

|                              |                 |
|------------------------------|-----------------|
| Contact Mating Area Length   | 5.84 mm[.23 in] |
| Mating Square Post Dimension | .64 mm[.025 in] |



|                                                         |                  |
|---------------------------------------------------------|------------------|
| PCB Contact Termination Area Plating Material Thickness | 2.54 μm[100 μin] |
| Contact Mating Area Plating Material Thickness          | 2.54 μm[100 μin] |
| PCB Contact Termination Area Plating Material Finish    | Matte            |
| Contact Shape & Form                                    | Square           |
| Contact Mating Area Plating Material Finish             | Matte            |
| PCB Contact Termination Area Plating Material           | Tin              |
| Contact Base Material                                   | Brass            |
| Contact Mating Area Plating Material                    | Tin              |
| Contact Type                                            | Pin              |
| Contact Current Rating (Max)                            | 3 A              |

Termination Features

|                                             |                       |
|---------------------------------------------|-----------------------|
| Square Termination Post & Tail Dimension    | .64 mm[.025 in]       |
| Termination Post & Tail Length              | 3.3 mm[.13 in]        |
| Termination Method to Printed Circuit Board | Through Hole - Solder |

Mechanical Attachment

|                          |                       |
|--------------------------|-----------------------|
| Mating Alignment Type    | Latched, Polarization |
| Mating Retention         | With                  |
| PCB Mount Retention Type | Hold-Down             |
| Mating Retention Type    | Hold-Down             |
| Connector Mounting Type  | Board Mount           |
| Mating Alignment         | With                  |
| PCB Mount Alignment      | Without               |
| PCB Mount Retention      | With                  |

Housing Features

|                    |                |
|--------------------|----------------|
| Housing Material   | Thermoplastic  |
| Centerline (Pitch) | 2.54 mm[.1 in] |

Dimensions

|                             |                  |
|-----------------------------|------------------|
| Connector Length            | 43.18 mm[1.7 in] |
| Connector Height            | 6.99 mm[.275 in] |
| PCB Thickness (Recommended) | 1.57 mm[.062 in] |

Usage Conditions

|                            |      |
|----------------------------|------|
| Housing Temperature Rating | High |
|----------------------------|------|



Operating Temperature Range

-65 – 105 °C[-85 – 221 °F]

Operation/Application

|                     |        |
|---------------------|--------|
| Circuit Application | Signal |
|---------------------|--------|

Industry Standards

|                        |                       |
|------------------------|-----------------------|
| Approved Standards     | CSA LR7189, UL E28476 |
| UL Flammability Rating | UL 94V-0              |

Packaging Features

|                    |           |
|--------------------|-----------|
| Packaging Quantity | 12        |
| Packaging Type     | Box, Tube |

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2023 (235)<br>Candidate List Declared Against: JUNE 2023 (235)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                             |
| Solder Process Capability                     | Reflow solder capable to 260°C                                                                                                  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 1-487526-5  
016 HOUSING FFC RCPT 100CL SR

TE Part # 6-103645-5  
16 MTE RCPT SR LATCH .100CL

Also in the Series

AMPMODU MTE

Insertion & Extraction Tools(1)

PCB Connector Shrouds(40)

PCB Headers & Receptacles(763)

Ribbon Connector Accessories(1)

Standard Rectangular Connectors(2)

Wire-to-Board Connector Assemblies  
& Housings(585)

Wire-to-Board Connector Contacts(32)

Customers Also Bought

TE Part #103906-3  
04 MTE HDR SRRA LATCH .100CL

TE Part #5-103669-2  
03 MTE HDR SRST LATCH W/HLDWN

TE Part #5212044-1  
5 CIRC DIN RCPT GRND SHLD

TE Part #1-534237-2  
14 MODII VRT SR CE 100/115

TE Part #1-2176329-1  
CRGP 1210 68R 1%

TE Part #5555164-1  
MJ,LPF,R/A,8P,TRAY

TE Part #86434-1  
MOD I RECP LP



Documents

Product Drawings

16 MTE HDR SRRA LATCH W/HLDWN

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_6-103672-5\_AL.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_6-103672-5\_AL.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_6-103672-5\_AL.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPMODU\_INTERCONNECTION\_SYSTEM\_SECTION5\_CONT

English

AMPMODU MTE INTERCONNECT SYSTEM

English

Product Specifications

Application Specification

English