



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **80**

Number of Rows: **2**

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Header
Connector System	Board-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Connector Contact Load Condition	Fully Loaded
PCB Mount Orientation	Vertical
Number of Positions	80
Number of Rows	2
Board-to-Board Configuration	Parallel

Electrical Characteristics

Dielectric Withstanding Voltage (Max)	500 VAC
Insulation Resistance	5000 MΩ
Operating Voltage	30 VAC

Body Features

Connector Profile	Standard
Primary Product Color	Black



Contact Features

Mating Square Post Dimension	.38 mm[.015 in]
PCB Contact Termination Area Plating Material Thickness	3.81 – 6.35 µm[150 – 250 µin]
PCB Contact Termination Area Plating Material Finish	Matte
Contact Shape & Form	Rectangular
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Copper Alloy
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
Contact Type	Pin
Contact Current Rating (Max)	3.6 A

Termination Features

Round Termination Post & Tail Diameter	.38 mm[.015 in]
Termination Post & Tail Length	3.68 mm[.145 in]
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

Mating Retention	With
Mating Retention Type	Latching
Mating Alignment	With
Mating Alignment Type	Polarization
PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	1.27 mm[.05 in]
Housing Material	LCP

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
PCB Thickness (Recommended)	1.57 mm[.062 in]

Usage Conditions

Housing Temperature Rating	High
----------------------------	------



Operating Temperature Range

-65 – 105 °C[-85 – 221 °F]

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Rating	Recognized
Agency/Standard	CSA, UL
Approved Standards	CSA LR7189, UL E28476
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	9
Packaging Type	Box, Tube

Other

Position Locations Omitted	0
----------------------------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 260°C







Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





 <p>TE Part # 8-487937-0 080 HOUSING FFC 50CL DR LATCH</p>	 <p>TE Part # 5-104078-7 80 SYSTEM 50 RCPT ASSY DRST SN</p>	 <p>TE Part # 3-111196-3 80 RCPT SYSTEM 50 30 DPLX</p>	 <p>TE Part # 5-104550-8 80 SYS50 SURFMNT DRST RCPT SN</p>
 <p>TE Part # 5-104744-4 80 SYSTEM 50 RCPT ASSY DRST SN</p>	 <p>TE Part # 5-147378-7 80 SYS50 SMT RCP DR SHD SN</p>		

Also in the Series | AMPMODU System 50



PCB Headers & Receptacles(1012)

Customers Also Bought

 <p>TE Part #1676221-1 RN 0805 1K0 0.1% 10PPM CUT LENGTH</p>	 <p>TE Part #7-215460-4 MICRO-MATCH FSID P</p>	 <p>TE Part #2-111446-3 040 UNIV I/O 30DP NO EARS</p>	 <p>TE Part #1625892-4 3W SM M/OX 5% R33</p>
---	--	--	---



TE Part #6-1393224-1
RY213012

TE Part #102536-5
14 AMPMODU MT COVER DR .100CL

TE Part #5-103956-5
4X6 MTE RCPT SR LATCH .100CL

TE Part #810033-000
2019D0309-0

TE Part #3-928336-4
2X17P MODU-MT SOCKET HOUSING

Documents

Product Drawings

80 SYSTEM 50 HDR DRST SHRD SN

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-104666-5_AD.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5-104666-5_AD.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-104666-5_AD.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPMODU_INTERCONNECTION_SYSTEM_SECTION3AND4

English

Product Specifications

Application Specification

English

Product Environmental Compliance

TE Material Declaration

5-104666-5

PCB Mount Header, Vertical, Board-to-Board, 80 Position, 1.27 mm [.05 in] Centerline,
Fully Shrouded, Gold, Through Hole - Solder, AMPMODU System 50



English