




Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**

Connector & Housing Type: **Receptacle**

Number of Positions: **4**

Centerline (Pitch): **3.96 mm [.156 in]**

Number of Rows: **1**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	4
Number of Rows	1

Body Features

Connector Profile	Low
Primary Product Color	Black

Contact Features

Contact Type	Socket
--------------	--------

Housing Features

Housing Material	Thermoplastic
Centerline (Pitch)	3.96 mm[.156 in]

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 102099-5 MOD I RECP STMPD	 TE Part # 181299-2 MOD 1 CONTACT REC	 TE Part # 181299-1 MOD I CRIMP CONTACT	 TE Part # 87116-2 MOD I KEYING PLUG
 TE Part # 102099-2 MOD I RECP PLTD 30 SEL	 TE Part # 102103-3 MOD I RECP LP	 TE Part # 102103-2 MOD I RECP LP	 TE Part # 102106-2 MOD I RECP LP

Also in the Series | AMPMODU MOD 1



Automotive Terminals(6)	Board-to-Board Connector Contacts (107)	Board-to-Board Jumpers & Shunts(5)	Insertion & Extraction Tools(1)
PCB Connector Keying(2)	PCB Headers & Receptacles(358)	Wire-to-Board Connector Assemblies & Housings(44)	Wire-to-Board Connector Contacts(2)

Customers Also Bought

TE Part #34974 PIDG Ring Tongue Terminals	TE Part #5745395-2 HD-20 RCPT 9P RA 318 FFSCRLK	TE Part #8-1437627-5 G12KB=BUTTON GUARD KNURL BLACK	TE Part #207444-8 METRIMATE PIN HEADER ASSY,18P
TE Part #2267473-2 SIZE 17 PERIPHERAL SEAL, CPC	TE Part #364915-E STVC 96 M ABC VVV 4-00 0606 * * 247 E007	TE Part #464271-E STVE 160 M ABCDE VVVV 4-00 0606 * 8360	

Documents

Product Drawings
04 MODI CRMP S-I HSG SR .156CL

English

Datasheets & Catalog Pages
AMPMODU_INTERCONNECTION_SYSTEM_SECTION_6_7AND8

English

Product Specifications



Application Specification

English

AMPMODU Mod I Receptacle Crimp Contact

English

Product Environmental Compliance

Product Compliance Document

English

Product Compliance Document

English