




this crimp contact should be processed with:

locator 09 99 000 0638
hand crimping tool 09 99 000 0509

surface specification				
pl	Ni [µm]	NiP [µm] (P=10,5-13%)	ΣNi+NiP [µm]	Au [µm]
1	min. 1,5	min. 1,5	max. 5,5	min. 0,15

	All Dimensions in mm Original Size DIN A4	Scale 10:1	Free size tol.			Ref.	
		Sub.					
	All rights reserved	Created by HASSE	Inspected by FRIESENH	Standardisation	Date 2021-08-30	State Final Release	
	Department EL PD						
HARTING D-32339 Espelkamp		Title M12-P-CON-1.5-AWG19/0.75 mm ² -M				Doc-Key / ECM-Nr. 100752423/UGD/002/C 500000201785	
		Type TB	Number 21011009963			Rev. C	Page 1/1