

3EXM4 ✓ ACTIVE

Corcom | Corcom M


TE Internal #: 6609131-8

Multi-Function Inlet Filters, Power Entry Module, Quad AC Input,  
No Switch, Filter Shield, Right Angle, 3A Current Rating, Corcom M

[View on TE.com >](#)



EMI & EMC Solutions > EMI Filters > Multi-Function Inlet Filters > CORCOM M SERIES MULTI-FUNCTION INLET FIL



Filter Type: Power Entry Module

Input Voltage Selection: Quad AC

Filter Switch Type: No Switch

Filter Shield Type: Filter Shield

Product Orientation: Right Angle

[All CORCOM M SERIES MULTI-FUNCTION INLET FIL \(28\)](#)

## Features

### Product Type Features

Ground Choke Option	No
Filter Type	Power Entry Module
Filter Switch Type	No Switch
Output Termination Type	.110" FASTON
Filtering Requirements	Filtered
Filter Connector Type	IEC 320/C-14

### Configuration Features

Fuse Options	Dual, Single
--------------	--------------

### Electrical Characteristics

Input Voltage Selection	Quad AC
Leakage Current (Max) (120VAC, 60Hz)	300 µA
Leakage Current (Max) (250VAC, 50Hz)	500 µA
Current Rating	3 A

Operating Voltage	100 VAC, 120 VAC, 230 VAC, 240 VAC
-------------------	------------------------------------

#### Body Features

Filter Shield Type	Filter Shield
Product Orientation	Right Angle

#### Mechanical Attachment

Panel Mount Feature Type	Flanged
--------------------------	---------

#### Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

#### Other

EMI Filters Comment	Voltage Selectable
---------------------	--------------------

#### Product Compliance


For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

#### Compatible Parts



TE Part # CAT-C8114-M1  
CORCOM M SERIES MULTI-FUNCTION INLET FIL


## Also in the Series | Corcom M



EMI & EMC Accessories(2)



Multi-Function Inlet Filters(28)



Potentiometers(5)

## Customers Also Bought



TE Part #327717  
PIDG SPD 22-16 COMM 22-18MIL 4



TE Part #640907-1  
RECEPT, PIDG FASTON 12-10 250



TE Part #3-640621-4  
04P MTA100 CONN ASSY F/T NATL



TE Part #2-6609028-1  
30VK6C=F7358C S0



TE Part #NB07196001  
BATTU-12.7/6.1-A1-2-51MM



TE Part #T4171210505-001  
M12, FRONT MOUNTING, MALE, D, 5P, 0.2M WIRE



TE Part #8-34176-1  
TERMINAL, PG SPD 12-10 10



TE Part #1-1393030-4  
SSRD-240D25 = PANEL MOUNT, 25A, 240VAC



TE Part #EM7492-000  
X2-11.0-0-FSP-SM

## Documents

### Product Drawings

[3EXM4=F8120](#)

English

---

### CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_6609131-8\\_C1.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_6609131-8\\_C1.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_6609131-8\\_C1.2d\\_dxf.zip](#)

English

### 3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Datasheets & Catalog Pages

[1654001\\_CORCOM\\_PRODUCT\\_GUIDE](#)

English

[1654001\\_CORCOM\\_PRODUCT\\_GUIDE\\_M\\_SERIES](#)

English

[Corcom Combined Selector Charts](#)

English