


Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**

Connector & Housing Type: **Plug**

Connector System: **Cable-to-Cable, Cable-to-Panel**

Number of Positions: **104**

Centerline (Pitch): **3.81 mm [.15 in]**

## Features

### Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Plug
Connector System	Cable-to-Cable, Cable-to-Panel
Sealable	No
Connector & Contact Terminates To	Wire & Cable

### Configuration Features

Number of Positions	104
Number of Power Positions	104
Number of Signal Positions	104
Number of Rows	8

### Electrical Characteristics

Operating Voltage	250 VDC
-------------------	---------

### Contact Features

Contact Current Rating (Max)	13 A
------------------------------	------

Contact Retention Within Housing	With
Contact Type	Pin

#### Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

#### Mechanical Attachment

Strain Relief	Without
Panel Mount Feature	With
Panel Mount Feature Type	Screw Mount
Connector Mounting Type	Panel Mount

#### Housing Features

Centerline (Pitch)	3.81 mm [.15 in]
Housing Color	Black
Housing Material	Phenolic GF

#### Dimensions

Connector Height	71.88 mm [2.83 in]
Product Width	28.7 mm [1.13 in]
Product Length	107.37 mm [4.227 in]
Wire Size	.05 – 2 mm <sup>2</sup>
Row-to-Row Spacing	3.3 mm [.13 in]

#### Usage Conditions

Operating Temperature Range	-55 – 150 °C [-67 – 302 °F]
-----------------------------	-----------------------------

#### Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

#### Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire

#### Packaging Features

Packaging Quantity	1
Packaging Method	Carton

#### Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

## Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 201532-4  
RECEPT BLOCK,104 POSN,M SERIES


Also in the Series | **AMP M Series**




Board-to-Board Jumpers &amp; Shunts(7)




Rack &amp; Panel Connectors(1)



Rectangular Connector Hardware(51)



Rectangular Power Connectors(66)



Standard Edge Connectors(2)

## Customers Also Bought

TE Part #205690-2  
SOC. BLOCK 28 POS. SPL.TE Part #967398-000  
D-406-0001TE Part #207234-1  
UNASSM JS KIT,M SERIESTE Part #608802-1  
CABLE TIE MOUNT, 4-WAY, 3/4" SQ"TE Part #201369-4  
75 POS. PIN HOODTE Part #36154  
PIDG R 22-16 COMM 22-18 MIL 10TE Part #CB5440-000  
XFFR-15X4TE Part #201501-1  
SPIROL PIN

## Documents

### CAD Files

### 3D PDF

English

#### Customer View Model

[ENG\\_CVM\\_201692-6\\_AN.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_201692-6\\_AN.3d\\_igs.zip](#)

English

**Customer View Model**[ENG\\_CVM\\_201692-6\\_AN.3d\\_stp.zip](#)

English

**Customer View Model**[ENG\\_CVM\\_CVM\\_201692-6\\_AY.3d\\_jgs.zip](#)

English

**Customer View Model**[ENG\\_CVM\\_CVM\\_201692-6\\_AY.3d\\_stp.zip](#)

English

**Customer View Model**[ENG\\_CVM\\_CVM\\_201692-6\\_AY.2d\\_dxf.zip](#)

English

**3D PDF**

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.**Datasheets & Catalog Pages**[M\\_SERIES\\_PIN\\_AND\\_SOCKET\\_CONNECTORS](#)

English

**Instruction Sheets**[Instruction Sheet \(U.S.\)](#)

English

[M Series 104-Position Plug & Receptacle Connectors w/Center Fasteners](#)

English

**Agency Approvals**[Agency Approval Document](#)

English