

APPLICABLE STANDARD		SPECIFICATIONS			
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C <sup>(1)</sup>	STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C <sup>(2)</sup>	
	OPERATING HUMIDITY RANGE	40 % TO 80 %	STORAGE HUMIDITY RANGE	40 % TO 70 % <sup>(2)</sup>	
	VOLTAGE	200 V AC	APPLICABLE CABLE	AWG #26 TO #36	
	CURRENT	2 A	INSULATION	—	

	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
REMARK					
(1) TEMPERATURE RISE INCLUDED WHEN ENERGIZED.			APPROVED	HS. OKAWA	15. 06. 08
(2) THIS STORAGE INDICATES A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE THE BOARD MOUNTED.			CHECKED	HT. YAMAGUCHI	15. 06. 08
Unless otherwise specified, refer to MIL-STD-1344.			DESIGNED	MT. ITANO	15. 06. 08
			DRAWN	MT. ITANO	15. 06. 08
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-081901-00-00
		SPECIFICATION SHEET	PART NO.	A4B-15S-2C	
		HIROSE ELECTRIC CO., LTD.	CODE NO.	CL622-0311-7-00	1/1