



Wire-end ferrules, Max. wire cross-section: 0.5 mm², Length: 6 mm, Colour: natural

Business data

|                                            |               |
|--------------------------------------------|---------------|
| Article number                             | 2216.0        |
| Article name                               | H 0,5/6       |
| GTIN (EAN)                                 | 4044211050399 |
| Packaging unit                             | 1000          |
| Quantity unit                              | PC            |
| Weight per piece (not including packaging) | 0.03 g        |
| Weight per piece (including packaging)     | 0.04 g        |
| Unit of weight                             | G             |
| Customs number                             | 85369010      |
| Country of origin                          | DE            |
| Product description                        | Ferrules      |
| Colour                                     | Natural       |

### Technical data

#### Dimensions

|                               |         |
|-------------------------------|---------|
| Length                        | 6 mm    |
| Diameter of copper pipe       | 1 mm    |
| Diameter of feed-in funnel    | 2.1 mm  |
| Wall thickness of copper pipe | 0.15 mm |

#### Connection data

|                              |                     |
|------------------------------|---------------------|
| Wire cross-section, max.     | 0.5 mm <sup>2</sup> |
| Wire cross-section AWG, max. | 20                  |
| Stripping length             | 6 mm                |

#### Materials

|                           |                                |
|---------------------------|--------------------------------|
| Copper pipe               | Copper alloy                   |
| Surface                   | Galvanically tin-plated, shiny |
| Working temperature, max. | 120 °C                         |

#### Environmental Product Compliance

|                                |            |
|--------------------------------|------------|
| REACH Conform                  | yes        |
| REACH Reference date           | 2023-06-14 |
| REACH Candidate Substance Note | No         |
| RoHS Conform                   | yes        |

---

**Approvals**

---

**Standards and regulations**

---

|                  |     |
|------------------|-----|
| DIN 46228-1:1992 | yes |
|------------------|-----|

---

---

**Media**

---

---

**Accessories**

---