




Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Connector & Housing Type: **Receptacle**
Number of Positions: **1**
Terminal Orientation: **Straight**
UL Flammability Rating: **UL 94V-0**

Features

Product Type Features

Connector System	Wire-to-Wire
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	1
---------------------	---

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	With

Mechanical Attachment

Mating Alignment Type	Polarization
Mating Alignment	With



Housing Features

Housing Material	Nylon 6/6
------------------	-----------

Dimensions

Product Length	24.3 mm[.956 in]
----------------	------------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

Glow Wire Rating	GWT 750°C (Without Flame)
Approved Standards	CSA Certified
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability









Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides








on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 176448-1 187 HSG. PL MKII TAB NAT</p>	 <p>TE Part # 173974-1 187 HSG. PL MKII REC. NAT</p>	 <p>TE Part # 176448-6 POSITIVE LOCK 187 (4.8 MM) HOUSING</p>	 <p>TE Part # 1-176448-1 187 POSITIVE LOCK MK-II TAB HSG 1POS</p>
 <p>TE Part # 1-521119-1 POSILOCK HSG.,250 SRS,MKIII,2P,V0, NAT</p>	 <p>TE Part # 2-174712-1 PL MK2 2P 187 HOUSING REC NATURAL</p>	 <p>TE Part # 3-172076-1 POSITIVE LOCK 250 HOUSING RECEPTACLE</p>	 <p>TE Part # 3-173974-7 PL MKII 187 REC HSG 1P NYLON GWT RED</p>

Also in the Series | Mark II

 <p>Automotive Housings(8)</p>	 <p>Automotive Terminals(22)</p>	 <p>Crimp Terminal Housings(76)</p>	 <p>Insertion & Extraction Tools(2)</p>
 <p>Quick Disconnects(57)</p>			

Also in the Series | Positive Lock 187



Crimp Terminal Housings(86)



Insertion & Extraction Tools(2)



Insulation Boots & Sleeves(7)



Quick Disconnects(57)


Customers Also Bought




TE Part #1473413-1
TH/.025 CONNECTOR SYSTEM,
HOUSING




TE Part #62896-1
MAG-MATE POKE-IN TAB 018 PTPBR



TE Part #1123343-1
025 REC CONTACT



TE Part #3-173974-6
PL MKII 187 REC HSG 1P NYLON
GWT BLU



TE Part #3-173974-7
PL MKII 187 REC HSG 1P NYLON
GWT RED

Documents

Product Drawings

PL MKII 187 REC HSG 1P NYLON GWT NAT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-173974-1_P.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-173974-1_P.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-173974-1_P.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



[Product Specifications](#)

[Engineering Report](#)

English