



Connectors > Circular Connectors > Circular Connector Accessories > Circular Connector Caps & Covers



Connector Cover Type: **Protective Cap**

Compatible With Connector Shell Size: **11, 13**

Operating Temperature Range: **-20 – 80 °C [-4 – 176 °F]**

Features

Product Type Features

Connector Cover Type	Protective Cap
----------------------	----------------

Body Features

Primary Product Material	Thermoplastic
Primary Product Color	Yellow

Usage Conditions

Operating Temperature Range	-20 – 80 °C[-4 – 176 °F]
-----------------------------	--------------------------

Operation/Application

Compatible With Connector Shell Size	11, 13
--------------------------------------	--------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235)



Candidate List Declared Against: JAN 2023 (233)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-AM71-C8398EE Mini Circular Plastic Connectors (CPC)	TE Part # CAT-AM71-C8398M CPC Connectors, Series 2	TE Part # CAT-AM71-C8398J Cable/Panel Mount Connector, CPC Series 1	TE Part # CAT-AM71-C8398Y One-Piece Connector, Sealed, CPC Series 1
TE Part # CAT-AM71-C8398K Circular Connector, Environmentally Sealed, CPC Series 6	TE Part # CAT-AM71-C8398DD Connectors, CPC Series 2, with Posted Contacts	TE Part # 1-796407-1 CPC PSTD RCPT, 11-4, R/A LF	TE Part # 205841-1 CPC RECPT ASSEMBLY SIZE 11-8



Documents

Product Drawings

CAP, CPC, SIZE 11 RECP & 13 PLUG, YELLOW

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-2407269-4_2.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_1-2407269-4_2.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2407269-4_2.3d_igs.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Datasheet - CPC Protective Caps

English

Instruction Sheets

Instruction Sheet (U.S.)

English