

C5SMF-Rxx,Gxx,Bxx:Screen Master® 5-mm Oval LEDs



PRODUCT DESCRIPTION

These oval LEDs are specifically designed • for full-color video screens, digital billboards and passenger-information signs. The oval-shaped radiation pattern and high luminous intensity ensure that these devices are excellent for bright sunlight or low power consumption outdoor applications.

These lamps are made with an advanced optical-grade epoxy that offers superior high-temperature and high-moisture-resistance performance in outdoor signal and sign applications. The encapsulation resin contains anti-UV material in order to reduce the effects of long-term exposure to direct sunlight.

FEATURES

- Size (mm): 5
- Color and Typical Dominant Wavelength: Red (621nm) Green(527nm) Blue(470nm)
- Luminous Intensity (mcd)
 C5SMF-RJF/RJE: (1100-4180)
 C5SMF-GJF/GJE: (2130-8200)
 C5SMF-BJF/BJE: (550-2130)
- Lead Free
- RoHS Compliant

APPLICATIONS

- Electronic Signs & Signals (ESS)
- Full Color Video Screen
- · Digital Billboards
- Motorway Signs
- · Variable Message Sign (VMS)
- · Advertising Signs
- · Petrol Signs



ABSOLUTE MAXIMUM RATINGS ($T_A = 25$ °C)

Items	Symbol	Absolute Maximum Rating		Unit
		Red	Green and Blue	
Forward Current	I _F	50 Note1	35	mA
Peak Forward Current Note2	I _{FP}	200	100	mA
Reverse Voltage	$V_{_{\mathrm{R}}}$	5	5	V
Power Dissipation	$P_{_{D}}$	130	140	mW
Operation Temperature	T _{opr}	-40 ^	+95	°C
Storage Temperature	T _{stg}	-40 ~	+100	°C
Lead Soldering Temperature	T_{sol}	(3 m	bulb)	
Electrostatic Discharge Classification (MIL-STD-883E)	ESD	Class 2		

Note:

- 1. For long term performance the drive currents between 10mA and 30mA are recommended. Please contact Cree LED sales representative for more information on recommended drive conditions.
- 2. Pulse width ≤ 0.1 msec, duty $\leq 1/10$.

TYPICAL ELECTRICAL & OPTICAL CHARACTERISTICS ($T_A = 25$ °C)

Characteristics	Color	Symbol	Condition	Unit	Minimum	Typical	Maximum
Fam	Red	$V_{_{\rm F}}$	I _F = 20 mA	V		2.1	2.6
Forward Voltage	Blue/Green	$V_{_{\rm F}}$	I _F = 20 mA	V		3.4	4.0
Reverse Current	Red	I _R	V _R = 5 V	μΑ			100
Reverse Current	Blue/Green	I _R	V _R = 5 V	μΑ			100
	Red	$\lambda_{_{D}}$	I _F = 20 mA	nm	619	621	624
Dominant Wavelength	Green	$\lambda_{_{\mathrm{D}}}$	I _F = 20 mA	nm	520	527	535
	Blue	$\lambda_{_{D}}$	I _F = 20 mA	nm	460	470	475
	Red	I _v	I _F = 20 mA	mcd	1100	2200	
Luminous Intensity	Green	I_{V}	I _F = 20 mA	mcd	2130	4400	
	Blue	I_{v}	I _F = 20 mA	mcd	550	1100	

^{*} Continuous reverse voltage can cause LED damage.



INTENSITY BIN LIMIT

	Red (20 mA) - C	:5SMF-RJF/RJE		Green (20 mA) - C5SMF-GJF/GJE					
Bin Code	Sub-Bin	Min.(mcd)	Max.(mcd)	Bin Code	Sub-Bin	Min.(mcd)	Max.(mcd)		
	T1	1100	1205		V1	2130	2347		
TO	T2	1205	1310	1/0	V2	2347	2564		
10	T3	1310	1415	V0	V3	2564	2781		
	T4	1415	1520		V4	2781	3000		
	U1 1520 1672		W1	3000	3295				
	U2	1672 1824	\WO	W2	3295	3590			
U0	U3	1824	1976	W0	W3	3590	3885		
	U4	1976	2130		W4	3885	4180		
	V1	2130	2347		X1	4180	4600		
VO	V2	2347	2564	VO	X2	4600	5020		
VU	V3	2564	2781	X0	X3	5020	5440		
	V4	2781	3000		X4	5440	5860		
	W1	3000	3295		Y1	5860	6445		
W0	W2	3295	3590	Y0	Y2	6445	7030		
VVU	W3	3590	3885	YU	Y3	7030	7615		
	W4	3885	4180		Y4	7615	8200		

^{*} Tolerance of measurement of luminous intensity is ±15%



INTENSITY BIN LIMIT

	Bule (20 mA) - C5SMF-BJF/BJE								
Bin Code	Sub-Bin	Min.(mcd)	Max.(mcd)						
	R1	550	605						
DO.	R2	605	660						
R0	R3	660	715						
	R4	715	770						
	S1	770	852						
S0	S2	852	934						
50	S3	934	1017						
	S4	1017	1100						
	T1	1100	1205						
T0	T2	1205	1310						
10	ТЗ	1310	1415						
	T4	1415	1520						
	U1	1520	1672						
U0	U2	1672	1824						
00	U3	1824	1976						
	U4	1976	2130						

^{*} Tolerance of measurement of luminous intensity is ±15%

COLOR BIN LIMIT

Red (20 mA)		Green (20 mA)			Blue (20 mA)			
Bin Code	Min.(nm)	Max.(nm)	Bin Code	Min.(nm)	Max.(nm)	Bin Code	Min.(nm)	Max.(nm)
RB	619	624	G7	520	525	В3	460	465
			G8	525	530	B4	465	470
			G9	530	535	B5	470	475

^{*} Tolerance of measurement of dominant wavelength is ±1 nm.



ORDER CODE TABLE

C5SMF-RJF/RJE

	Luminous Intensity (mcd)			Dominant			a		
Color	Kit Number	Min. Max.		Color Bin	Min. (nm)	Min. (nm) Color Bin		Package	Standoff
Red	C5SMF-RJF-CT0W0BB1	1100	4180	RB	619	RB	624	Bulk	Yes
Red	C5SMF-RJF-CT14QBB1		utive sub-bins: - U2(1824)	RB	619	RB	624	Bulk	Yes
Red	C5SMF-RJF-CT34QBB1		utive sub-bins: - U4(2130)	RB	619	RB	624	Bulk	Yes
Red	C5SMF-RJF-CU14QBB1		utive sub-bins: - V2(2564)	RB	619	RB	624	Bulk	Yes
Red	C5SMF-RJE-CT0W0BB1	1100	4180	RB	619	RB	624	Bulk	No
Red	C5SMF-RJE-CT14QBB1		utive sub-bins: - U2(1824)	RB	619	RB	624	Bulk	No
Red	C5SMF-RJE-CT34QBB1		utive sub-bins: - U4(2130)	RB	619	RB	624	Bulk	No
Red	C5SMF-RJE-CU14QBB1		utive sub-bins: - V2(2564)	RB	619	RB	624	Bulk	No
Red	C5SMF-RJF-CT0W0BB2	1100	4180	RB	619	RB	624	Ammo	Yes
Red	C5SMF-RJF-CT14QBB2		utive sub-bins: - U2(1824)	RB	619	RB	624	Ammo	Yes
Red	C5SMF-RJF-CT34QBB2	Any 4 consec T3(1310)	utive sub-bins: - U4(2130)	RB	619	RB	624	Ammo	Yes
Red	C5SMF-RJF-CU14QBB2	Any 4 consecution U1(1520)	utive sub-bins: - V2(2564)	RB	619	RB	624	Ammo	Yes
Red	C5SMF-RJE-CT0W0BB2	1100	4180	RB	619	RB	624	Ammo	No
Red	C5SMF-RJE-CT14QBB2	Any 4 consecutive sub-bins: T1(1100) - U2(1824)		RB	619	RB	624	Ammo	No
Red	C5SMF-RJE-CT34QBB2	Any 4 consecutive sub-bins: T3(1310) - U4(2130)		RB	619	RB	624	Ammo	No
Red	C5SMF-RJE-CU14QBB2		utive sub-bins: - V2(2564)	RB	619	RB	624	Ammo	No

Notes:

- The above kit numbers represent order codes that include multiple intensity-bin and color-bin codes. Only one intensity-bin code and one color-bin code will be shipped on each reel. single intensity-bin, single color-bin codes will not be orderable.
- · Please refer to the HB LED Lamp Reliability Test Standards document for reliability test conditions.
- Please refer to the HB LED Lamp Soldering & Handling document for information about how to use this LED product safely.



ORDER CODE TABLE

C5SMF-GJF/GJE

Color	Kit Number	Luminous Intensity (mcd)			Dominant		- Package	Standoff	
Color	Kit Number	Min.	Max.	Color Bin	Color Bin Min. (nm)		Max. (nm)	Раскаде	Standon
Green	C5SMF-GJF-CV0Y0791	2130	8200	G7	520	G9	535	Bulk	Yes
Green	C5SMF-GJF-CW34Q7T1		utive sub-bins: - X4(5860)	Any 1 c	olor bin from G	7 (520nm) to G	8 (530nm)	Bulk	Yes
Green	C5SMF-GJF-CX14Q7T1		utive sub-bins: - Y2(7030)	Any 1 c	olor bin from G	7 (520nm) to G	8 (530nm)	Bulk	Yes
Green	C5SMF-GJE-CV0Y0791	2130	8200	G7	520	G9	535	Bulk	No
Green	C5SMF-GJE-CW34Q7T1		utive sub-bins: - X4(5860)	Any 1 c	olor bin from G	7 (520nm) to G	8 (530nm)	Bulk	No
Green	C5SMF-GJE-CX14Q7T1		utive sub-bins: - Y2(7030)	Any 1 c	olor bin from G	7 (520nm) to G	8 (530nm)	Bulk	No
Green	C5SMF-GJF-CV0Y0792	2130	8200	G7	520	G9	535	Ammo	Yes
Green	C5SMF-GJF-CW34Q7T2		utive sub-bins: - X4(5860)	Any 1 c	olor bin from G	7 (520nm) to G	8 (530nm)	Ammo	Yes
Green	C5SMF-GJF-CX14Q7T2	Any 4 consect X1(4180)	utive sub-bins: - Y2(7030)	Any 1 color bin from G7 (520nm) to G8 (530nm)			8 (530nm)	Ammo	Yes
Green	C5SMF-GJE-CV0Y0792	2130	8200	G7	520	G9	535	Ammo	No
Green	C5SMF-GJE-CW34Q7T2	Any 4 consecutive sub-bins: W3(3590) - X4(5860)		Any 1 color bin from G7 (520nm) to G8 (530nm)			8 (530nm)	Ammo	No
Green	C5SMF-GJE-CX14Q7T2		utive sub-bins: - Y2(7030)	Any 1 c	olor bin from G	7 (520nm) to G	8 (530nm)	Ammo	No

Notes:

- The above kit numbers represent order codes that include multiple intensity-bin and color-bin codes. Only one intensity-bin code and one color-bin code will be shipped on each reel. single intensity-bin, single color-bin codes will not be orderable.
- Please refer to the HB LED Lamp Reliability Test Standards document for reliability test conditions.
- · Please refer to the HB LED Lamp Soldering & Handling document for information about how to use this LED product safely.



ORDER CODE TABLE

C5SMF-BJF/BJE

Color	Kit Number	Luminous Int	ensity (mcd)	ity (mcd) Dominant Wavelength Package		Dominant Wavelength		Daakana	Standoff
Color	KIT NUMBER	Min.	Max.	Color Bin	Color Bin Min. (nm) Color Bin Max. (nm)			Раскаде	Stalluoli
Blue	C5SMF-BJF-CR0U0351	550	2130	В3	460	B5	475	Bulk	Yes
Blue	C5SMF-BJF-CR0U0451	550	2130	B4	465	B5	475	Bulk	Yes
Blue	C5SMF-BJF-CT14Q3T1	Any 4 consect T1(1100)	utive sub-bins: - U2(1824)	Any 1 c	olor bin from B	3 (460nm) to B4	4 (470nm)	Bulk	Yes
Blue	C5SMF-BJF-CT14Q4T1		utive sub-bins: - U2(1824)	Any 1 c	olor bin from B	4 (465nm) to B	5 (475nm)	Bulk	Yes
Blue	C5SMF-BJF-CT34Q3T1	Any 4 consect T3(1310)	utive sub-bins: - U4(2130)	Any 1 c	olor bin from B	3 (460nm) to B4	4 (470nm)	Bulk	Yes
Blue	C5SMF-BJF-CT34Q4T1	Any 4 consect T3(1310)	utive sub-bins: - U4(2130)	Any 1 c	olor bin from B	4 (465nm) to B	5 (475nm)	Bulk	Yes
Blue	C5SMF-BJE-CR0U0351	550	2130	В3	460	B5	475	Bulk	No
Blue	C5SMF-BJE-CR0U0451	550	2130	B4	465	B5	475	Bulk	No
Blue	C5SMF-BJE-CT14Q3T1		Any 4 consecutive sub-bins: T1(1100) - U2(1824) Any 1 color bin from B3 (460nm) to B4 (470nm)				4 (470nm)	Bulk	No
Blue	C5SMF-BJE-CT14Q4T1		utive sub-bins: - U2(1824)	Any 1 c	olor bin from B	4 (465nm) to B	5 (475nm)	Bulk	No
Blue	C5SMF-BJE-CT34Q3T1	Any 4 consect T3(1310)	utive sub-bins: - U4(2130)	Any 1 c	olor bin from B	3 (460nm) to B4	4 (470nm)	Bulk	No
Blue	C5SMF-BJE-CT34Q4T1	Any 4 consect T3(1310)	utive sub-bins: - U4(2130)	Any 1 c	olor bin from B	4 (465nm) to B	5 (475nm)	Bulk	No
Blue	C5SMF-BJF-CR0U0352	550	2130	В3	460	B5	475	Ammo	Yes
Blue	C5SMF-BJF-CR0U0452	550	2130	B4	465	B5	475	Ammo	Yes
Blue	C5SMF-BJF-CT14Q3T2	Any 4 consect T1(1100)	utive sub-bins: - U2(1824)	Any 1 c	olor bin from B	3 (460nm) to B4	1 (470nm)	Ammo	Yes
Blue	C5SMF-BJF-CT14Q4T2	Any 4 consect T1(1100)	utive sub-bins: - U2(1824)	Any 1 c	olor bin from B	4 (465nm) to B	5 (475nm)	Ammo	Yes
Blue	C5SMF-BJF-CT34Q3T2	Any 4 consect T3(1310)	utive sub-bins: - U4(2130)	Any 1 c	olor bin from B	3 (460nm) to B4	1 (470nm)	Ammo	Yes
Blue	C5SMF-BJF-CT34Q4T2	Any 4 consect T3(1310)	utive sub-bins: - U4(2130)	Any 1 c	olor bin from B	4 (465nm) to B	5 (475nm)	Ammo	Yes
Blue	C5SMF-BJE-CR0U0352	550	2130	В3	460	B5	475	Ammo	No
Blue	C5SMF-BJE-CR0U0452	550	2130	B4	465	B5	475	Ammo	No
Blue	C5SMF-BJE-CT14Q3T2	Any 4 consect T1(1100)	utive sub-bins: - U2(1824)	Any 1 c	olor bin from B	3 (460nm) to B4	4 (470nm)	Ammo	No
Blue	C5SMF-BJE-CT14Q4T2		utive sub-bins: - U2(1824)	Any 1 color bin from B4 (465nm) to B5 (475nm)			Ammo	No	
Blue	C5SMF-BJE-CT34Q3T2		utive sub-bins: - U4(2130)	Any 1 c	olor bin from B	3 (460nm) to B4	4 (470nm)	Ammo	No
Blue	C5SMF-BJE-CT34Q4T2	Any 4 consect T3(1310)	utive sub-bins: - U4(2130)	Any 1 c	olor bin from B	4 (465nm) to B	5 (475nm)	Ammo	No


Notes:

- The above kit numbers represent order codes that include multiple intensity-bin and color-bin codes. Only one intensity-bin code and one color-bin code will be shipped on each reel. single intensity-bin, single color-bin codes will not be orderable.
- · Please refer to the HB LED Lamp Reliability Test Standards document for reliability test conditions.
- · Please refer to the HB LED Lamp Soldering & Handling document for information about how to use this LED product safely.



GRAPHS

The data below are collected from statistical figures that do not necessarily correspond to the actual parameters of each single LED. Hence, these data will be changed without further notice.







FIG.3a RED REVERSE CURRENT VS. REVERSE VOLTAGE.






FIG.5 RELATIVE LUMINOUS INTENSITY VS. WAVELENGTH.





FIG.2 RELATIVE LUMINOUS INTENSITY VS. FORWARD CURRENT



Ir(uA)
FIG.3b BLUE & GREEN REVERSE CURRENT VS.
REVERSE VOLTAGE.



FORWARD DC CURRENT VS AMBIENT TEMPERATURE (Tjmax=105 °C)




FIG.6 RED & BLUE&GREEN FAR FIELD PATTERN




MECHANICAL DIMENSIONS

All dimensions are in mm. Tolerance is ±0.25 mm unless otherwise noted.


An epoxy meniscus may extend about 1.5 mm down the leads.

Burr around bottom of epoxy may be 0.5 mm max.

C5SMF-RJF/GJF/BJF:



C5SMF-RJE/GJE/BJE:



NOTES

Lead Frame Materials

Ag-plated and Lead-free Solder-plated iron.

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Cree LED representative or from the Product Ecology section of the Cree LED website.

Vision Advisory


WARNING: Do not look at an exposed lamp in operation. Eye injury can result.



KIT NUMBER SYSTEM

Cree LED lamps are tested and sorted into performance bins. A bin is specified by ranges of color, forward voltage, and brightness. Sorted LEDs are packaged for shipping in various convenient options.

Cree LEDs are sold by order codes in combinations of bins called kits. Order codes are configured in the following manner:



 $^{^{\}star}$ Please contact our sales representative for ordering information.




SOLDERING GUIDELINES

The LED soldering specification is shown below(suitable for both leaded solder & lead-free solder):

	Manual Soldering	Solder Dipping				
Soldering iron	35 W max	Preheat	110 °C max			
Townserver	300 00 may	Preheat time	60 seconds max			
Temperature	300 °C max	Solder-bath temperature	260 °C Max			
Soldering time	3 seconds max	Dipping time	5 seconds max			
Position	Not less than 3 mm from the base of the package.	Position	Not less than 3 mm from the base of the package.			

- Manual soldering onto the PCB is not recommended because soldering time is uncontrollable.
- The recommended wave soldering is as below:




- · Do not apply any stress to the LED package, particularly when heated.
- · Only bottom preheat is suggested & should not preheat on top in order to reduce thermal stress experienced by the LEDs.
- · The LEDs must not be re used once they have been extracted from PCB.
- After soldering the LEDs, the package should be protected from mechanical shock or vibration until the LEDs have reached 40 °C or below.
- Precautions must be taken as mechanical stress on the LEDs may be caused by PCB warpage or from the clinching and cutting of the LED leads.
- · When it is necessary to clam the LEDs during soldering, it is important to ensure no mechanical stress is exerted on the LEDs.
- · Cut the LED lead at normal room temperature. Lead cutting at high temperature may cause failure of the LEDs.
- · Please refer to the HB LED Lamp Soldering & Handling document for information about how to use this LED product safely.



PACKAGING

- · The LEDs are packed in cardboard boxes after packaging in normal or anti-electrostatic bags.
- · Cardboard boxes will be used to protect the LEDs from mechanical shock during transportation.
- The boxes are not water resistant, and they must be kept away from water and moisture.
- Max 500 pcs per bulk and Max 2500 pcs per ammo.

Bulk Pack Packaging Type:



Ammo Pack Packaging Type:

