




MTA 156

TE Internal #: 1-643071-4
PCB Connector Covers, 14 Position, .156 in [3.96 mm] Centerline,
Nylon, Standard Product Profile, -55 – 105 °C [-67 – 221 °F], MTA
156

[View on TE.com >](#)

Connectors > PCB Connectors > PCB Connector Accessories > PCB Protection & Strain Relief > PCB Connector Covers



Number of Positions: 14
Centerline (Pitch): 3.96 mm [.156 in]
Primary Product Material: Nylon
Product Profile: Standard
Operating Temperature Range: -55 – 105 °C [-67 – 221 °F]

Features

Product Type Features

Product Profile	Standard
-----------------	----------

Configuration Features

Number of Positions	14
---------------------	----

Body Features

Primary Product Color	White
Primary Product Material	Nylon

Housing Features

Centerline (Pitch)	3.96 mm[.156 in]
--------------------	------------------

Usage Conditions

Compatible With IDC Installation Type Connector	Feed Thru
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-103156-WBHSM
Receptacle Housing: Wire-to-Board, with Mating Alignment, SL156



TE Part # CAT-103156-WBHSN
Receptacle Housing: Wire-to-Board, no Mating Alignment, SL 156







TE Part # 1-640445-4
14P MTA156 HDR ASSY FL/STR SN





TE Part # 1-640387-4
14P MTA156 HDR ASSY SQ R/A



 TE Part # 1-640385-4 14P MTA156 HDR ASSY SQ R/A	 TE Part # 4-641208-4 14P MTA156 HDR ASSY FL ST LF	 TE Part # 4-641119-4 14P MTA156 HDR ASSY FL/ST LF	 TE Part # 4-644617-4 14P MTA156 HDR ASSY PO RA FB LF
 TE Part # 643710-7 14P MTA156 HDR ASSY FL SN WO#5	 TE Part # 1-640388-4 14P MTA156 HDR ASSY RN STR F/L	 TE Part # 4-640427-4 14P MTA156 CONN ASSY 20AWG YEL	 TE Part # 4-640428-4 14P MTA156 CONN ASSY 22AWG RED
 TE Part # 4-640599-4 14P MTA156 CONN ASSY 18AWG ORA	 TE Part # 4-644615-4 14P MTA156 POL HDR ASSY LF	 TE Part # 4-643818-4 14P MTA156 CONN ASSY 20AWG YEL	 TE Part # 643710-4 14P MTA156 HDR ASSY W/O#7
 TE Part # 4-640426-4 14P MTA156 CONN ASSY 18AWG ORA	 TE Part # 4-643817-4 14P MTA156 CONN ASSY 18AWG LF	 TE Part # 1-640384-4 14P MTA156 HDR ASSY STR RND SN	 TE Part # 1-644752-4 14P MTA156 HDR ASSY SQ STR F/L

Also in the Series | MTA 156

 Insertion & Extraction Tools(1)	 PCB Connector Covers(88)	 PCB Connector Keying(2)	 PCB Connector Mounting(1)
--	---	--	--



PCB Headers & Receptacles(314)



Power Contacts(2)



Rectangular Power Connectors(698)



Standard Rectangular Connectors(337)



Wire-to-Board Connector Contacts(2)

Customers Also Bought




TE Part #2-326882-1
TERMINAL,PIDG R 16-14 6




TE Part #1-1879450-8
TE 500W 27R 5% Bracket



TE Part #1-66105-8
III+ SKT,24-20,30AU/FL,SMPACK



TE Part #5745653-3
DIECAST STRAIN RELIEF KIT,SZ 3



TE Part #643067-9
09P MTA156 MOLDED COVER



TE Part #321868
TERMINAL SOLIS RING 1/0 3/8




TE Part #3-644662-9
09P MTA156 CONN ASSY 22AWG LF



TE Part #3-644663-8
08P MTA156 CONN ASSY 20AWG LF



TE Part #4-644466-4
14P MTA156 CONN ASSY 20AWG YEL



TE Part #312160-1
WIRE INSERTER

Documents



Product Drawings

14P MTA156 FD-THRU COVER

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-643071-4_M.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-643071-4_M.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-643071-4_M.3d_stp.zip

English

3D PDF

English

Customer View Model

ENG_CVM_1-643071-4_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_1-643071-4_F.3d_igs.zip

English

Customer View Model

ENG_CVM_1-643071-4_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

Japanese

Application Specification

English

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

English

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

Japanese

Product Environmental Compliance

MD_1-643071-4_09192017014_dmtec

English

MD_1-643071-4_09192017014_dmtec

English



Instruction Sheets

Instruction Sheet (U.S.)

English