




Connectors > PCB Connectors > PCB Headers & Receptacles



Connector System: **Wire-to-Board**
Number of Positions: **2**
Number of Rows: **1**
Centerline (Pitch): **5 mm [.197 in]**
PCB Mount Orientation: **Vertical**

Features

Product Type Features

Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
PCB Connector Assembly Type	PCB Mount Header

Configuration Features

Keying & Polarized Position Locations	1C
Number of Columns	2
Number of Positions	2
Number of Rows	1
PCB Mount Orientation	Vertical

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Body Features



Primary Product Color	Black
-----------------------	-------

Contact Features

PCB Contact Termination Area Plating Material Thickness	2 µm[78.74 µin]
Contact Layout	Inline
Mating Tab Width	6.3 mm[.248 in]
Mating Tab Thickness	.8 mm[.032 in]
Contact Underplating Material Thickness	1.27 µm[50 µin]
Contact Mating Area Plating Material Thickness	2 µm[78.74 µin]
PCB Contact Termination Area Plating Material Finish	Matte
Contact Shape & Form	Rectangular
Contact Mating Area Plating Material Finish	Matte
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Copper Alloy
Contact Mating Area Plating Material	Tin
Contact Type	Tab
Contact Current Rating (Max)	16 A

Termination Features

Square Termination Post & Tail Dimension	.8 mm[.032 in]
Termination Post & Tail Length	3.5 mm[.138 in]
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

PCB Mount Alignment Type	Polarizing Pegs
Mating Alignment Type	Keyed, Polarization
Mating Retention	With
Mating Retention Type	Latch
Connector Mounting Type	Board Mount
Mating Alignment	With
PCB Mount Alignment	With
PCB Mount Retention	Without

Housing Features

Housing Material	Nylon
------------------	-------



Centerline (Pitch)	5 mm[.197 in]
--------------------	---------------

Dimensions

Connector Length	12.3 mm[.48 in]
Connector Height	12.8 mm[.5 in]
Connector Width	14.9 mm[.58 in]
PCB Thickness (Recommended)	1.5 mm[.06 in]

Usage Conditions

Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Agency/Standard	UL
Approved Standards	UL E28476
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	153
Packaging Type	Loose Piece

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability









Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent



chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-2232001-2 2P, RAST 5 Tab Header, THV,black, silver	 TE Part # 2-2232043-2 2P, RAST 5 Tab Header, THV	 TE Part # 1-1971954-2 2P, RAST 5 Tab Header, THV	 TE Part # 1-2232043-2 2P, RAST 5 Tab Header, THV
 TE Part # 1969522-1 ASSY, TAB HDR, EXT, 7MM, 6.35 SER, 3 POS	 TE Part # 2-2232045-2 2P, RAST 5 Tab Header, THV	 TE Part # 2232000-2 2P, RAST 5 Tab Header, THV,black, tin	 TE Part # 3-2232045-2 2P, RAST 5 Tab Header, THV
 TE Part # 4-2232043-2 2P, RAST 5 Tab Header, THV	 TE Part # 4-2232045-2 2P, RAST 5 Tab Header, THV	 TE Part # 5-2232043-2 2P, RAST 5 Tab Header, THV	 TE Part # 7-2232043-2 2P, RAST 5 Tab Header, THV
 TE Part # 9-2232043-2 2P, RAST 5 Tab Header, THV	 TE Part # 1955659-2 Assembly Positive Lock RAST 5, Spl Ver		

Also in the Series | RAST 5 IDC Connectors



Automotive Terminals(8)




Connector Contacts(12)



Crimp Terminal Housings(41)




Insertion & Extraction Tools(1)



PCB Headers & Receptacles(417)



Rectangular Connector Housings(1)



Standard Edge Connectors(34)



Standard Rectangular Connectors(68)




Wire-to-Board Connector Assemblies & Housings(214)



Wire-to-Board Connector Contacts(2)


Customers Also Bought




TE Part #282087-1
AMP SUPERSEAL 1.5 SERIES 3P PL




TE Part #1-1123723-7
3.96 EP HDR ASSY 7P(NATURAL)




TE Part #1586040-2
2P VAL-U-LOK VRT HDR W/P V0




TE Part #281934-2
SINGLE WIRE SEAL



TE Part #1586042-2
2P VAL-U-LOK R/A HDR V0



TE Part #183025-1
MINI MIC RECPT C



TE Part #1586044-2
2P VAL-U-LOK R/A HDR SCR MT V0



TE Part #6-1123723-7
3.96 EP HDR ASSY 7P(GREEN)

Documents



Product Drawings

2P, RAST 5 Tab Header, THV,black, Tin

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2232000-2_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2232000-2_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2232000-2_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Agency Approvals

VDE Certificate

English