

# **Quectel M66**

### Ultra-small Quad-band **GSM/GPRS** Module



M66 is an ultra-small quad-band GSM/GRPS module using LCC castellation packaging on the market. Based on the latest 2G chipset, it has the optimal performance in SMS & Data transmission and audio service even in harsh environment. The ultracompact 15.8mm × 17.7mm × 2.3mm profile makes it a perfect platform for size sensitive applications.

M66 adopts surface mount technology, making it an ideal solution for durable and rugged designs. The low profile and small size of LCC package makes sure M66 can be easily embedded into size-constrained applications, and provides reliable connectivity with applications. This kind of package is ideally suited for large-scale manufacturing which has strict requirements for cost and efficiency.

The compact form factor, low power consumption and extended temperature make M66 a best choice for M2M applications such as wearable devices, automotive, industrial PDA, personal tracking, wireless POS, smart metering, telematics, and more.



### Kev **Benefits**

- Extremely compact quad-band GSM/GPRS module
- Easier soldering process with LCC package
- Power consumption as low as 1.3mA
- Support Voice, Bluetooth, QuecFOTA<sup>™</sup> and Quectel OpenCPU functions
- Embedded powerful Internet service protocols, multiple Sockets & IP addresses







Quad-band

GPRS Multi-slot Class 12

Extended Temperature Range: -40°C ~ +85°C









Embedded Internet Services Protocols







Quectel Enhanced AT Commands

**Digital Audio** 

Bluetooth 3.0

## **Quectel M66**

Ultra-small Quad-band GSM/GPRS Module



15.8 mm

Frequency Band

Quad-band: 850/ 900/ 1800/ 1900MHz

#### Data

GPRS Class 12: Max. 85.6kbps (Downlink) Max. 85.6kbps (Uplink) Coding Schemes:

CS 1, 2, 3. 4 USSD Non-transparent Mode

#### SMS

Point-to-point MO and MT SMS Cell Broadcast Text and PDU Mode

#### Voice

Speech Codec Modes: Half Rate (HR) Full Rate (FR) Enhanced Full Rate (EFR) Adaptive Multi-Rate (AMR) Echo Arithmetic: Echo Cancellation Echo Suppression Noise Reduction

#### Interfaces

(U)SIM Card Interface:
3.0V/ 1.8V
UART × 3
Analog Audio Channel:
2 Output Channels and 1 Input Channel

#### Bluetooth:

BT 3.0 Profile: SPP, HFP PCM × 1 RTC × 1 ADC × 1 Antenna Pad: × 2 (GSM Antenna Pad and Bluetooth Antenna Pad)

#### **Enhanced Features**

eCall Jamming Detection DTMF Audio Play/ Audio Record QuecFOTA<sup>™</sup> QuecCell QuecLocator QuecFile OpenCPU<sup>™</sup> RIL for Android MUX Bluetooth

#### **Electrical & Sensitivity**

Output Power: Class 4 (2W @850/ 900MHz) Class 1 (1W @1800/ 1900MHz) Consumption: 1.3mA @DRX=5 1.2mA @DRX=9 Sensitivity: GSM850: -109dBm

GSM900: -109dBm DCS1800: -109dBm PCS1900: -109dBm Supply Voltage: 3.3V~4.6V, 4.0V Typ.

H

2.3 mr

#### Software Features

BT3.0 Protocols: TCP/ UDP/ PPP/ FTP/ HTTP/ SMTP/ CMUX/ SSL

0

#### **General Features**

GPRS Multi-slot Class: Class 12 GPRS Mobile Station: Class B Temperature Range: -40°C ~ +85°C Dimensions: 17.7mm × 15.8mm × 2.3mm LCC Package Weight: Approx. 1.3g GSM 07.07, 07.05 and other Enhanced AT Commands

#### Approvals

RoHS Compliant CE/UCRF (Europe) DoC (Russia) Anatel (Brazil) ICASA (South Africa)

Copyright© 2017 Quectel Wireless Solutions Co., Ltd.All Rights Reservedhttp://www.quectel.comHQ address: 7<sup>th</sup> Floor, Hongye Building, No.1801 HongmeiRoad, Xuhui District, Shanghai 200233, ChinaTel: +86 21 51086236Fax: +86 21 54453668Email: info@quectel.com

