



Terminals & Splices > Spade Terminals > AMPOWER TERMINAL 2 STUD HOLES LONG BAR



Spade Terminal Type: **Rectangular Tongue Terminal**
Wire Size: **650000 – 750000 CMA**
Stud Size: **1/2, M12**
Stud Diameter: **14.27 mm [.562 in]**

[All AMPOWER Terminal 2 Stud Holes Long Bar \(9\)](#)

Features

Product Type Features

Stud Size	1/2, M12
Sealable	No

Configuration Features

Number of Holes	2
-----------------	---

Contact Features

Spade Terminal Type	Rectangular Tongue Terminal
Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	650000 – 750000 CMA
Stud Diameter	14.27 mm[.562 in]
Tongue Thickness	6.1 mm[.24 in]
Product Length	161.29 mm[6.35 in]



Barrel Inside Diameter	29.51 mm[1.161 in]
------------------------	--------------------

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	25
Packaging Method	Box

Other

Terminals & Splices Comment	Electrodeposited Tin Plate per MIL-T-10727., Two Crimps necessary.
-----------------------------	--

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part



numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 46757-2
HYP8 AMPOWER 700MCM DIE SET

TE Part # 53686-3
TERMINAL,AMPOWER 700MCM 1/2 sight hole

Also in the Series | AMPOWER

Busbar Connectors(13)

Knife Disconnects(14)

PCB Headers & Receptacles(2)

Power Cable Assemblies(7)

Power Contacts(1)

Quick Disconnects(1)

Rectangular Power Connectors(6)

Spade Terminals(139)

Splices(39)

Customers Also Bought



Documents

Product Drawings

[TERMINAL,AMPPOWER 700MCM 1/2](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_53686-2_L.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_53686-2_L.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_53686-2_L.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMPPOWER Terminals and Splices Flyer](#)

English

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[UL Report](#)

English